

SILVYN® FLEXILOK 90° M

SILVYN® FLEXILOK 90° M -

90°
small purchasing unit



CE UK CA



(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SILVYN® FLEXILOK 90° M

UV

UL FILENUMBER E308201

90°

가

PG threaded versions are to be found in the online catalogue

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

:

(RAL 7031)

(RAL 9005), UV

:

PA66

가:

IP 66

:

-40°C ~ +120°C

가 VAT

가 가 .

(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SILVYN® FLEXILOK 90° M

		(thread)	(mm)	SILVYN® FPAS	OØ (mm)	/ PU
SILVYN® FLEXILOK 90° M						
68100100	16 x 1.5	12		FPAS 16	15,8	10
68100105	20 x 1.5	13		FPAS 16	15,8	10
68100106	20 x 1.5	13		FPAS 20	20	10
68100110	20 x 1.5	13		FPAS 21	21,2	10
68100114	25 x 1.5	15		FPAS 25	25	10
68100115	25 x 1.5	15		FPAS 28	28,5	10
68100119	32 x 1.5	16		FPAS 32	32	10
68100120	32 x 1.5	16		FPAS 34	34,5	10
SILVYN® FLEXILOK 90° M						
68100125	16 x 1.5	12		FPAS 16	15,8	10
68100130	20 x 1.5	13		FPAS 16	15,8	10
68100131	20 x 1.5	13		FPAS 20	20	10
68100135	20 x 1.5	13		FPAS 21	21,2	10
68100139	25 x 1.5	15		FPAS 25	25	10
68100140	25 x 1.5	15		FPAS 28	28,5	10
68100144	32 x 1.5	16		FPAS 32	32	10
68100145	32 x 1.5	16		FPAS 34	34,5	10