

SILVYN® FLEXILOK 90° PG

SILVYN® FLEXILOK 90° PG - PG

90°
small purchasing unit



CE UK CA



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® FLEXILOK 90° PG

UV

UL FILENUMBER E308201

PG
90°

가

ETIM 5:	ETIM 5.0 Class-ID: EC001176
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC001176
	ETIM 6.0 Class :
:	IEC EN 61386-23
:	(RAL 7031)
	(RAL 9005), UV
:	PA66
가:	IP 66
:	-40°C ~ +120°C

가 VAT 가 가 .

(24.04.2024)



SILVYN® FLEXILOK 90° PG

	(thread)	(mm)	SILVYN® FPAS	OØ (mm)	/ PU
SILVYN® FLEXILOK 90° PG					
68100150	10		FPAS 16	15,8	10
68100155	10		FPAS 16	15,8	10
68100160	10		FPAS 16	15,8	10
68100170	10		FPAS 21	21,2	10
68100165	11		FPAS 16	15,8	10
68100175	11		FPAS 21	21,2	10
68100180	12		FPAS 28	28,5	10
68100185	12		FPAS 34	34,5	10
SILVYN® FLEXILOK 90° PG					
68100190	10		FPAS 16	15,8	10
68100195	10		FPAS 16	15,8	10
68100200	10		FPAS 16	15,8	10
68100210	10		FPAS 21	21,2	10
68100205	11		FPAS 16	15,8	10
68100215	11		FPAS 21	21,2	10
68100220	12		FPAS 28	28,5	10
68100225	12		FPAS 34	34,5	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16