

SILVYN® FPAG 90° PG

SILVYN® FPAG 90° PG - SILVYN® FPAS



90°

SILVYN® FPAS

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® FPAG 90° PG

UV
가

UL FILENUMBER E308201

PG
90°
가

ETIM 5:	ETIM 5.0 Class-ID: EC001176
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC001176
	ETIM 6.0 Class :
:	IEC EN 61386-23
:	(RAL 7031)
	(RAL 9005), UV
:	PA66
가:	IP 66
:	-50°C ~ +135°C

가 VAT 가 가 .

(24.04.2024)



SILVYN® FPAG 90° PG

	SILVYN® FPAS	/ PU
SILVYN® FPAG 90° PG		
55506715	10	10
55506725	13	10
55506735	16	10
55506745	16	10
55506755	18	10
55506815	21	10
55506765	21	10
55506775	28	10
55506785	34	10
55506795	42	1
55506805	54	1
55506825	67	1
SILVYN® FPAG 90° PG		
55506710	10	10
55506720	13	10
55506730	16	10
55506740	16	10
55506750	18	10
55506810	21	10
55506760	21	10
55506770	28	10
55506780	34	10
55506790	42	1
55506800	54	1
55506820	67	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16