

# SILVYN® MAXI PA

SILVYN® MAXI PA



**CE UK CA**



UL FILENUMBER E308201

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# SILVYN® MAXI PA

, 6

ETIM 5:	ETIM 5.0 Class-ID: EC001175
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC001175
	ETIM 6.0 Class :
:	PA 12 가
:	(RAL 7001)
	(RAL 9005), UV
:	PA 6
	UL 94 HB
:	-40°C ~ +115°C
	+150°C

가 VAT 가 가 .



# SILVYN® MAXI PA

	( )	ID x OD mm	(mm)	SILVYN® AFG-PA/AFW-PA	PU ring (m)
SILVYN® MAXI PA					
61791150	70	66.5 x 79.2	170	70	10
61791160	95	91 x 106	225	95	10
SILVYN® MAXI PA					
61791155	70	66.5 x 79.2	170	70	10
61791165	95	91 x 106	225	95	10

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16