

SILVYN® HCC

SILVYN® HCC



-

, ,



SILVYN® HCC

UV

ETIM 5:

ETIM 5.0 Class-ID: EC001175

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001175

ETIM 6.0 Class :

:

(RAL 9005), UV

:

PA6

:

-25°C ~ +100°C

가 VAT 가 가 .

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® HCC

	()	ID x OD mm	(mm)	SILVYN®FPAG-M / FLEXILOK-M	SILVYN®HG-M	PU ring (m)
SILVYN® HCC						
61793970	13	9.8 x 13.0	25	16 + 20	-	50
61793980	16	11.8 x 16.0	30	16 + 20	-	50
61793990	20	14.8 x 20.0	40	20	-	50
61794000	25	19.1 x 25.0	50	25	-	50
61794010	32	24.3 x 32	65	32	-	25
61794020	40	30.2 x 40	85	-	40	25
61794030	50	40.1 x 50	110	-	50	25
61794035	63	52.5 x 63	130	-	63	25