

# SILVYN® HG-M

SILVYN® HG-M - SILVYN® HCC



SILVYN® HCC

UV

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

(RAL 9005), UV

:

PA6

가:

IP 65

:

-25°C ~ +100°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## SILVYN® HG-M

가 VAT 가 가 .

(24.04.2024)



## SILVYN® HG-M

		mm	(thread) (mm)	SILVYN® HCC	/ PU
55501650	40 x 1,5	53	15	40	20
55501660	50 x 1,5	57.4	15	50	16
55501670	63 x 1,5	74	20	63	8

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16