

SILVYN® SPLIT COS

SILVYN® SPLIT COS



SILVYN® SPLIT :

UV

ETIM 5:

ETIM 5.0 Class-ID: EC001171

ETIM 5.0 Class :

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® SPLIT COS

ETIM 6:

:
:
:

ETIM 6.0 Class-ID: EC001171

ETIM 6.0 Class :

(RAL 9005), UV

PA

-40°C ~ +120°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® SPLIT COS

	()	Ø (mm)	SILVYN® SPLIT	/ PU
61806693	6	M3	6	100
61806690	10	M3	10	100
61806676	10	M5	10	100
61806694	11	M3	11	100
61806700	14	M3	14	100
61806677	14	M5	14	50
61806695	16	M5	16	50
61806696	16	M6	16	50
61806710	20	M5	20	50
61806678	20	M6	20	50
61806720	23	M5	23	50
61806679	23	M6	23	50
61806697	29	M5	29	50
61806698	29	M6	29	50
61806730	37	M6	37	20
61806740	45	M6	45	20
61806699	70	M6	70	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16