



SILVYN® SPLIT GMP-M

SILVYN® SPLIT GMP-M

SILVYN® SPLIT

UV

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

(RAL 9005), UV

:

PA

:

-40°C ~ +120°C

가 VAT 가 가 .

(15.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® SPLIT GMP-M

		/ PU
SILVYN® SPLIT GMP-M ()		
61806686	16 x 1.5	100
61806687	20 x 1.5	100
61806688	25 x 1.5	50
61806689	32 x 1.5	50
61806691	40 x 1.5	25
61806692	50 x 1.5	25

(15.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16