

SILVYN® SPLIT

SILVYN® SPLIT , 가



(PA6)

(23.04.2024)

SILVYN® SPLIT

’ ’

(SILVYN® SPLIT PP UV)

가

ETIM 5:

ETIM 5.0 Class-ID: EC001175

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001175

ETIM 6.0 Class :

:

12 ()

ETFE (+200°C)

:

(RAL 9005), UV

:

6 (PA6)

(PP)

가:

IP 43, SILVYN® SPLIT COV

:

PA6 : -40°C ~ +120°C

PP : -40°C ~ +135°C

PP UV: -40°C ~ +105°C

가 VAT

가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® SPLIT

	()	ID x OD mm	(mm)	SILVYN® COV	PU (m)
SILVYN® SPLIT PA6					
61806621	6	6.3 x 10	15	-	50
61806620	10	8.8 x 13.5	15	M16/PG9	50
61806631	11	11 x 16.1	15	-	50
61806630	14	13.2 x 18.7	15	M20/PG13,5	50
61806641	16	16 x 21.5	20	-	50
61806640	20	20.2 x 25.7	25	M25/PG21	50
61806650	23	23.9 x 31.3	35	M32/PG29	50
61806651	29	27.3 x 36.0	35	-	25
61806660	37	32.5 x 41.9	40	M40/PG29	25
61806670	45	43.0 x 54.2	70	M50	25
61806671	70	66.5 x 79.8	95	-	10
61806672	100	88.0 x 103.5	100	-	10
61737403	10	8.8 x 13.5	15	M16/PG9	10
61737226	14	13.2 x 18.7	15	M20/PG13,5	10
61737227	20	20.2 x 25.7	25	M25/PG21	10
61737228	23	23.9 x 31.3	35	M32/PG29	10
61737229	37	32.5 x 41.9	40	M40/PG29	10
SILVYN® SPLIT PP					
61806615	6	6.3 x 10	15	-	50
61806625	10	8.4 x 13.4	15	M16/PG9	50
61806616	11	11 x 16.1	15	-	50
61806635	14	12.5 x 18.5	15	M20/PG13,5	50
61806617	16	16 x 21.5	20	-	50
61806645	20	19.2 x 25.3	20	M25/PG21	50
61806655	23	23.4 x 30.8	45	M32/PG29	50
61806618	29	27.3 x 35.5	50	-	25
61806665	37	31 x 41.4	60	M40/PG29	25
61806675	45	42.7 x 54	75	M50	25
61806619	70	66.0 x 79.5	95	-	10
61806622	100	87.5 x 102.5	100	-	10
SILVYN® SPLIT PP UV					

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® SPLIT

	()	ID x OD mm	(mm)	SILVYN® COV	PU (m)
61806100	6	6.3 x 10	15	-	50
61806110	10	8.4 x 13.4	15	M16/PG9	50
61806120	11	11 x 16.1	15	-	50
61806130	14	12.5 x 18.5	15	M20/PG13,5	50
61806140	16	16 x 21.5	20	-	50
61806150	20	19.2 x 25.3	20	M25/PG21	50
61806160	23	23.4 x 30.8	45	M32/PG29	50
61806170	29	27.3 x 35.5	50	-	25
61806180	37	31 x 41.4	60	M40/PG29	25
61806190	45	42.7 x 54	75	M50	25
61806200	70	66.0 x 79.5	95	-	10
61806210	100	87.5 x 102.5	100	-	10

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16