

FIPLOCK® ONE CLICK-M

FIPLOCK® PA6 / PA12

FIPLOCK® ONE CLICK-M

SKINTOP®



**CE UK
CA**



(24.04.2024)

FIPLOCK® ONE CLICK-M



IP

FIPLOCK®
PA6 / PA12
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

EN 45545-2 HL3

:

(RAL 7005)

(RAL 9005), UV

:

PA 6

가:

UL 94V-0

IP66/IP67/IP68/IP69

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



FIPLOCK® ONE CLICK-M

:

-45°C ~ +120°C

가 VAT 가 가 .

(24.04.2024)



FIPLOCK® ONE CLICK-M

		Clamping range in mm	SW 1/2 mm	(thread) (mm)	, S (mm)	FIPLOCK® PA6 / PA12		/ PU
61804874	M 16	5.0 - 9.0	22.0 / 20.0	8	1.0 - 4.0	10		10
61804875	M 16	5.0 - 9.0	22.0 / 22.0	8	1.0 - 4.0	12		10
61804876	M 20	7.0 - 13.0	27.0 / 22.0	8	1.0 - 4.0	12		10
61804877	M 20	7.0 - 13.0	27.0 / 27.0	8	1.0 - 4.0	17		10
61804878	M 25	9.0 - 17.0	32.0 / 27.0	8	1.0 - 4.0	17		10
61804879	M 25	9.0 - 17.0	32.0 / 36.0	8	1.0 - 4.0	23		6
61804880	M 32	11.0 - 20.0	40.0 / 36.0	8	1.0 - 4.0	23		6
61804881	M 32	11.0 - 20.0	40.0 / 41.0	8	1.0 - 4.0	29		6
61804882	M 16	5.0 - 9.0	22.0 / 20.0	8	1.0 - 4.0	10		10
61804883	M 16	5.0 - 9.0	22.0 / 22.0	8	1.0 - 4.0	12		10
61804884	M 20	7.0 - 13.0	27.0 / 22.0	8	1.0 - 4.0	12		10
61804885	M 20	7.0 - 13.0	27.0 / 27.0	8	1.0 - 4.0	17		10
61804886	M 25	9.0 - 17.0	32.0 / 27.0	8	1.0 - 4.0	17		10
61804887	M 25	9.0 - 17.0	32.0 / 36.0	8	1.0 - 4.0	23		6
61804888	M 32	11.0 - 20.0	40.0 / 36.0	8	1.0 - 4.0	23		6
61804889	M 32	11.0 - 20.0	40.0 / 41.0	8	1.0 - 4.0	29		6

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16