

FIPLOCK® ONE-C

FIPLOCK® PA6 / PA12

FIPLOCK[®] ONE-C



CE UK CA



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

FIPLOCK® ONE-C



IP

FIPLOCK®
PA6 / PA12
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

EN 45545-2 HL3

:

(RAL 7005)

(RAL 9005), UV

:

PA 6

가:

UL 94V-0

IP66/IP67/IP68/IP69

:

-45°C ~ +120°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



FIPLOCK® ONE-C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



FIPLOCK® ONE-C

	()	FIPLOCK® PA6 / PA12		/ PU
61805027	12	12		10
61805028	17	17		10
61805029	23	23		6
61805030	29	29		6
61805031	36	36		4
61805032	48	48		4
61805033	12	12		10
61805034	17	17		10
61805035	23	23		6
61805036	29	29		6
61805037	36	36		4
61805038	48	48		4

FIPLOCK® ONE-C



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16