

# FIPLOCK® ONE Flange 90°

FIPLOCK® PA6 / PA12

FIPLOCK<sup>®</sup> ONE Flange 90°



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# FIPLOCK® ONE Flange 90°



IP

FIPLOCK®  
PA6 / PA12  
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

EN 45545-2 HL3

:

(RAL 7005)

(RAL 9005), UV

:

PA 6

가:

UL 94V-0

IP66/IP67/IP68/IP69

:

-45°C ~ +120°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## FIPLOCK® ONE Flange 90°

가 VAT 가 가 .

(24.04.2024)



# FIPLOCK® ONE Flange 90°

	( )	FIPLOCK® PA6 / PA12	/ PU
61805134	17	17	10
61805135	23	23	6
61805136	29	29	6
61805137	36	36	4
61805138	48	48	4
61805139	17	17	10
61805140	23	23	6
61805141	29	29	6
61805142	36	36	4
61805143	48	48	4
61805144	17	17	10
61805145	23	23	6
61805146	29	29	6
61805147	36	36	4
61805148	48	48	4
61805149	17	17	10
61805150	23	23	6
61805151	29	29	6
61805152	36	36	4
61805153	48	48	4

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16