

FIPLOCK® ONE M

FIPLOCK® PA6 / PA12

FIPLOCK[®] ONE M



CE UK CA



(24.04.2024)

FIPLOCK® ONE M



IP

FIPLOCK®
PA6 / PA12
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

EN 45545-2 HL3

:

(RAL 7005)

(RAL 9005), UV

:

PA 6

UL 94V-0

가:

IP66/IP67/IP68/IP69

:

-45°C ~ +120°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



FIPLOCK® ONE M

가 VAT 가 가 .

(24.04.2024)



FIPLOCK® ONE M

			SW (mm)	(thread) (mm)	(mm)	FIPLOCK® PA6 / PA12		/ PU
FIPLOCK®ONE M,								
61804211	ASPA-07M12PB	12 x 1.5	17	11	7.2	7		10
61804212	ASPA-10M12PB	12 x 1.5	20	11	10	10		10
61804213	ASPA-10M16PB	16 x 1.5	20	11	10	10		10
61804214	ASPA-12M16PB	16 x 1.5	22	11	9	12		10
61804215	ASPA-10M20PB	20 x 1.5	20	11	10	10		10
61804216	ASPA-12M20PB	20 x 1.5	22	11	13	12		10
61804217	ASPA-17M20PB	20 x 1.5	27	11	13	17		10
61804218	ASPA-17M25PB	25 x 1.5	27	12	17.2	17		10
61804219	ASPA-23M25PB	25 x 1.5	36	12	18	23		6
61804220	ASPA-23M32PB	32 x 1.5	36	15	23	23		6
61804221	ASPA-29M32PB	32 x 1.5	41	15	25	29		6
61804222	ASPA-29M40PB	40 x 1.5	41	19	29	29		6
61804223	ASPA-36M40PB	40 x 1.5	52	19	31.9	36		4
61804224	ASPA-36M50PB	50 x 1.5	52	19	36	36		4
61804225	ASPA-48M50PB	50 x 1.5	65	19	41.9	48		4
61804226	ASPA-48M63PG	63 x 1.5	65	19	50.5	48		4
FIPLOCK®ONE M,								
61804227	ASPA-07M12PG	12 x 1.5	17	11	7.2	7		10
61804228	ASPA-10M12PG	12 x 1.5	20	11	10	10		10
61804229	ASPA-10M16PG	16 x 1.5	20	11	10	10		10
61804230	ASPA-12M16PG	16 x 1.5	22	11	9	12		10
61804231	ASPA-10M20PG	20 x 1.5	20	11	10	10		10
61804232	ASPA-12M20PG	20 x 1.5	22	11	13	12		10
61804233	ASPA-17M20PG	20 x 1.5	27	11	13	17		10
61804234	ASPA-17M25PG	25 x 1.5	27	12	17.2	17		10
61804235	ASPA-23M25PG	25 x 1.5	36	12	18	23		10
61804236	ASPA-23M32PG	32 x 1.5	36	15	23	23		10
61804237	ASPA-29M32PG	32 x 1.5	41	15	25	29		10
61804238	ASPA-29M40PG	40 x 1.5	41	19	29	29		10
61804239	ASPA-36M40PG	40 x 1.5	52	19	31.9	36		10
61804240	ASPA-36M50PG	50 x 1.5	52	19	36	36		10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



FIPLOCK® ONE M

			SW (mm)	(thread) (mm)	(mm)	FIPLOCK® PA6 / PA12		/ PU
61804241	ASPA-48M50PG	50 x 1.5	65	19	41.9	48		10
61804242	ASPA-48M63PG	63 x 1.5	65	19	50.5	48		10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16