

FIPLOCK®ONE M

FIPLOCK® PA6 / PA12

FIPLOCK®ONE M



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

FIPLOCK®ONE M



IP

FIPLOCK®
PA6 / PA12
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

EN 45545-2 HL3

:

(RAL 7005)

(RAL 9005), UV

:

PA 6

가:

UL 94V-0

IP66/IP67/IP68/IP69

:

-45°C ~ +120°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



FIPLOCK®ONE M

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

FIPLOCK®ONE M

		SW (mm)	(thread) (mm)	(mm)	FIPLOCK® PA6 / PA12	/ PU
61804531	12 x 1.5	20	5	5.6	10	10
61804532	16 x 1.5	20	5	9.5	10	10
61804533	16 x 1.5	22	5	9.5	12	10
61804534	20 x 1.5	22	6	12.4	12	10
61804535	20 x 1.5	27	6	13.2	17	10
61804536	25 x 1.5	27	7	16.6	17	10
61804537	25 x 1.5	36	7	18.1	23	6
61804538	32 x 1.5	36	8	23.3	23	6
61804539	32 x 1.5	41	8	25.1	29	6
61804540	40 x 1.5	41	8	29	29	6
61804541	40 x 1.5	52	8	33	36	4
61804542	50 x 1.5	52	9	36.5	36	4
61804543	50 x 1.5	65	9	42.7	48	4
61804544	63 x 1.5	65	10	50.5	48	4
61804545	12 x 1.5	20	5	5.6	10	10
61804546	16 x 1.5	20	5	9.5	10	10
61804547	16 x 1.5	22	5	9.5	12	10
61804548	20 x 1.5	22	6	12.4	12	10
61804549	20 x 1.5	27	6	13.2	17	10
61804551	25 x 1.5	27	7	16.6	17	10
61804552	25 x 1.5	36	7	18.1	23	6
61804553	32 x 1.5	36	8	23.3	23	6
61804554	32 x 1.5	41	8	25.1	29	6
61804555	40 x 1.5	41	8	29	29	6
61804556	40 x 1.5	52	8	33	36	4
61804557	50 x 1.5	52	9	36.5	36	4
61804558	50 x 1.5	65	9	42.7	48	4
61804559	63 x 1.5	65	10	50.5	48	4
61804561	12 x 1.5	20	10	5.6	10	10
61804562	16 x 1.5	20	10	9.5	10	10
61804563	16 x 1.5	22	10	9.5	12	10
61804564	20 x 1.5	22	10	12.4	12	10
61804565	20 x 1.5	27	10	13.2	17	10
61804566	25 x 1.5	27	11	16.6	17	10

FIPLOCK®ONE M

		SW (mm)	(thread) (mm)	(mm)	FIPLOCK® PA6 / PA12		/ PU
61804567	25 x 1.5	36	11	18.1	23		6
61804568	32 x 1.5	36	13	23.3	23		6
61804569	32 x 1.5	41	13	25.1	29		6
61804571	40 x 1.5	41	13	29	29		6
61804572	40 x 1.5	52	13	33	36		4
61804573	50 x 1.5	52	14	36.5	36		4
61804574	50 x 1.5	65	14	42.7	48		4
61804575	63 x 1.5	65	14	50.5	48		4
61804576	12 x 1.5	20	10	5.6	10		10
61804577	16 x 1.5	20	10	9.5	10		10
61804578	16 x 1.5	22	10	9.5	12		10
61804579	20 x 1.5	22	10	12.4	12		10
61804581	20 x 1.5	27	10	13.2	17		10
61804582	25 x 1.5	27	11	16.6	17		10
61804583	25 x 1.5	36	11	18.1	23		6
61804584	32 x 1.5	36	13	23.3	23		6
61804585	32 x 1.5	41	13	25.1	29		6
61804586	40 x 1.5	41	13	29	29		6
61804587	40 x 1.5	52	13	33	36		4
61804588	50 x 1.5	52	14	36.5	36		4
61804589	50 x 1.5	65	14	42.7	48		4
61804591	63 x 1.5	65	14	50.5	48		4

