

FIPLOCK®ONE PG

FIPLOCK® PA6 / PA12

FIPLOCK®ONE PG



(24.04.2024)

FIPLOCK®ONE PG



IP

FIPLOCK®  
PA6 / PA12  
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

EN 45545-2 HL3

:

(RAL 7005)

(RAL 9005), UV

:

PA 6

UL 94V-0

가:

IP66/IP67/IP68/IP69

:

-45°C ~ +120°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



FIPLOCK®ONE PG

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



FIPLLOCK®ONE PG

	PG	SW (mm)	(thread) (mm)	(mm)	FIPLLOCK® PA6 / PA12		/ PU
61804592	9	20	12	9.2	12		10
61804593	11	22	12	12.41	12		10
61804594	13.5	27	13	14	17		10
61804595	16	27	13	16.1	17		10
61804596	21	36	14	21.6	23		6
61804597	29	36	14	23.3	23		6
61804598	29	41	14	29	29		6
61804599	36	52	17	36.5	36		4
61804616	48	65	17	50.5	48		4
61804617	9	20	12	9.2	12		10
61804618	11	22	12	12.41	12		10
61804619	13.5	27	13	14	17		10
61804641	16	27	13	16.1	17		10
61804642	21	36	14	21.6	23		6
61804643	29	36	14	23.3	23		6
61804644	29	41	14	29	29		6
61804645	36	52	17	36.5	36		4
61804646	48	65	17	50.5	48		4

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

FIPLOCK®ONE PG



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16