

FIPLOCK® ONE NPT

FIPLOCK® PA6 / PA12

FIPLOCK[®] ONE NPT



CE UK CA



(02.05.2024)

FIPLOCK® ONE NPT



IP

FIPLOCK®
PA6 / PA12
가

360°

ETIM 5:	ETIM 5.0 Class-ID: EC001176
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC001176
	ETIM 6.0 Class :
:	IEC EN 61386-23
	EN 45545-2 HL3
:	(RAL 9005), UV
:	PA 6
	UL 94V-0
가:	IP66/IP67/IP68/IP69
:	-45°C ~ +120°C

(02.05.2024)



FIPLOCK® ONE NPT

가 VAT 가 가 .

(02.05.2024)



FIPLOCK® ONE NPT

	()	SW (mm)	(thread) (mm)	(mm)	FIPLOCK® PA6 / PA12	/ PU
61804261	NPT 3/8"	20	10.4	9.8	10	10
61804262	NPT 1/2"	22	13.5	13	12	10
61804263	NPT 1/2"	27	13.5	13	17	10
61804264	NPT 3/4"	36	14	18.4	23	6
61804265	NPT 1"	41	17.3	24.1	29	6
61804266	NPT 1 1/4"	52	18	32.2	36	4
61804267	NPT 1 1/2"	65	18.4	38.8	48	4
61804268	NPT 2"	65	19.2	50.8	48	4
61804269	NPT 3/8"	20	10.4	9.8	10	10
61804270	NPT 1/2"	22	13.5	13	12	10
61804271	NPT 1/2"	27	13.5	13	17	10
61804272	NPT 3/4"	36	14	18.4	23	6
61804273	NPT 1"	41	17.3	24.1	29	6
61804274	NPT 1 1/4"	52	18	32.2	36	4
61804275	NPT 1 1/2"	65	18.4	38.8	48	4
61804276	NPT 2"	65	19.2	50.8	48	4

(02.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16