

# FIPLOCK® ONE ST-NPT

FIPLOCK® PA6 / PA12

FIPLOCK<sup>®</sup> ONE ST-NPT

SKINTOP®



**CE UK CA**



(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# FIPLOCK® ONE ST-NPT



IP

FIPLOCK®  
PA6 / PA12  
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

EN 45545-2 HL3

:

(RAL 7005)

(RAL 9005), UV

:

PA 6

가:

UL 94V-0

IP66/IP67/IP68/IP69

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# FIPLOCK® ONE ST-NPT

:

-45°C ~ +120°C

가 VAT 가 가 .

(23.04.2024)



# FIPLOCK® ONE ST-NPT

	( )	Clamping range in mm	SW 1/2 mm	(thread) (mm)	FIPLOCK® PA6 / PA12	/ PU
61804861	NPT 3/8"	3.5 - 8.0	19.0 / 20.0	15	10	10
61804862	NPT 3/8"	3.5 - 8.0	19.0 / 22.0	15	12	10
61804863	NPT 1/2"	5.0 - 12.0	24.0 / 22.0	15	12	10
61804864	NPT 1/2"	5.0 - 12.0	24.0 / 27.0	15	17	10
61804865	NPT 3/4"	13.0 - 18.0	33.0 / 36.0	15	23	6
61804866	NPT 1"	14.0 - 25.0	42.0 / 41.0	15	29	6
61804867	NPT 3/8"	3.5 - 8.0	19.0 / 20.0	15	10	10
61804868	NPT 3/8"	3.5 - 8.0	19.0 / 22.0	15	12	10
61804869	NPT 1/2"	5.0 - 12.0	24.0 / 22.0	15	12	10
61804871	NPT 1/2"	5.0 - 12.0	24.0 / 27.0	15	17	10
61804872	NPT 3/4"	13.0 - 18.0	33.0 / 36.0	15	23	6
61804873	NPT 1"	14.0 - 25.0	42.0 / 41.0	15	29	6

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16