

FIPLOCK® ONE-Y

FIPLOCK® PA6 / PA12

FIPLOCK[®] ONE-Y



(24.04.2024)

FIPLOCK® ONE-Y



IP

FIPLOCK®
PA6 / PA12
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

EN 45545-2 HL3

:

(RAL 7005)

(RAL 9005), UV

:

PA 6

가:

UL 94V-0

IP66/IP67/IP68/IP69

:

-45°C ~ +120°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



FIPLOCK® ONE-Y

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

FIPLOCK® ONE-Y

	()	Ø (mm)	FIPLOCK® PA6 / PA12		/ PU
61804977	10-07-07	M4	7 / 10		10
61804978	12-10-10	M4	10 / 12		10
61804979	17-12-12	M5	12 / 17		10
61804980	23-17-17	M6	17 / 23		6
61804981	29-23-23	M6	23 / 29		6
61804982	36-29-29	M6	29 / 36		4
61804983	48-36-36	M6	36 / 48		4
61804984	10-07-07	M4	7 / 10		10
61804985	12-10-10	M4	10 / 12		10
61804986	17-12-12	M5	12 / 17		10
61804987	23-17-17	M6	17 / 23		6
61804988	29-23-23	M6	23 / 29		6
61804989	36-29-29	M6	29 / 36		4
61804991	48-36-36	M6	36 / 48		4

FIPLOCK® ONE-Y



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16