

FIPSPLIT® PA12

가

가

Hazard Level: HL 3



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



FIPSPPLIT® PA12

	()	ID x OD mm	(mm)	PU ring (m)
61803973	7	6.3 x 10.0	20	50
61803974	10	8.8 x 13.5	25	50
61803975	11	11.0 x 16.1	25	50
61803976	14	13.2 x 18.7	30	50
61803977	16	16.0 x 21.5	35	50
61803978	20	20.2 x 25.7	45	50
61803979	23	23.9 x 31.3	55	50
61803980	29	27.3 x 35.5	105	25
61803981	37	32.5 x 43.2	130	25
61803982	45	43.1 x 54.2	135	25
61803984	100	87.5 x 102.5	195	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16