

SILVYN® KLICK 90° M

SILVYN® KLICK-M - SILVYN® RILL



90°

SILVYN® RILL PA 6

SILVYN® RILL PA 12

UL FILENUMBER E308201

(26.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® KLICK 90° M

90°

가

PG threaded versions are to be found in the online catalogue

| | |
|---------|-----------------------------|
| ETIM 5: | ETIM 5.0 Class-ID: EC001176 |
| | ETIM 5.0 Class : |
| ETIM 6: | ETIM 6.0 Class-ID: EC001176 |
| | ETIM 6.0 Class : |
| : | (RAL 7001) |
| | (RAL 9005), UV |
| : | PA6 |
| 가: | IP 68 |
| | IP 69 |
| : | -40°C ~ +115°C |

가 VAT 가 가 .

(26.02.2024)



SILVYN® KLICK 90° M

| | | (thread) (mm) | (mm) | | SILVYN® RILL | / PU |
|---------------------|------------|------------------|------|------|--------------|------|
| SILVYN® KLICK 90° M | | | | | | |
| 55501110 | 10 x 1.0 | 12 | 6 | 10 | 10 | 50 |
| 55501120 | 12 x 1.5 | 12 | 8 | 13 | 13 | 50 |
| 55501130 | 16 x 1.5/1 | 12 | 12 | 13 | 13 | 50 |
| 55501140 | 16 x 1.5/2 | 12 | 12 | 15.8 | 16 | 50 |
| 55501150 | 20 x 1.5/1 | 13 | 15 | 15.8 | 16 | 50 |
| 55501160 | 20 x 1.5/2 | 13 | 15 | 21.2 | 21 | 50 |
| 55501170 | 25 x 1.5/1 | 13 | 18 | 21.2 | 21 | 50 |
| 55501180 | 25 x 1.5/2 | 13 | 18 | 28.5 | 28 | 25 |
| 55501190 | 32 x 1.5/1 | 15 | 24 | 28.5 | 28 | 25 |
| 55501200 | 32 x 1.5/2 | 15 | 24 | 34.5 | 34 | 10 |
| 55501210 | 40 x 1.5/1 | 15 | 32 | 34.5 | 34 | 10 |
| 55501220 | 40 x 1.5/2 | 15 | 32 | 42.5 | 42 | 10 |
| 55501230 | 50 x 1.5/1 | 16 | 39 | 42.5 | 42 | 10 |
| 55501240 | 50 x 1.5/2 | 16 | 39 | 54.5 | 54 | 5 |
| 55501250 | 63 x 1.5 | 16 | 53 | 54.5 | 54 | 5 |
| SILVYN® KLICK 90° M | | | | | | |
| 55501115 | 10 x 1.0 | 12 | 6 | 10 | 10 | 50 |
| 55501125 | 12 x 1.5 | 12 | 8 | 13 | 13 | 50 |
| 55501135 | 16 x 1.5/1 | 12 | 12 | 13 | 13 | 50 |
| 55501145 | 16 x 1.5/2 | 12 | 12 | 15.8 | 16 | 50 |
| 55501155 | 20 x 1.5/1 | 13 | 15 | 15.8 | 16 | 50 |
| 55501165 | 20 x 1.5/2 | 13 | 15 | 21.2 | 21 | 50 |
| 55501175 | 25 x 1.5/1 | 13 | 18 | 21.2 | 21 | 50 |
| 55501185 | 25 x 1.5/2 | 13 | 18 | 28.5 | 28 | 25 |
| 55501195 | 32 x 1.5/1 | 15 | 24 | 28.5 | 28 | 25 |
| 55501205 | 32 x 1.5/2 | 15 | 24 | 34.5 | 34 | 10 |
| 55501215 | 40 x 1.5/1 | 15 | 32 | 34.5 | 34 | 10 |
| 55501225 | 40 x 1.5/2 | 15 | 32 | 42.5 | 42 | 10 |
| 55501235 | 50 x 1.5/1 | 16 | 39 | 42.5 | 42 | 10 |
| 55501245 | 50 x 1.5/2 | 16 | 39 | 54.5 | 54 | 5 |
| 55501255 | 63 x 1.5 | 16 | 53 | 54.5 | 54 | 5 |

(26.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16