

SILVYN® KCLICK-GPZ

SILVYN® KCLICK-GPZ - SILVYN® RILL

가 PG



가
가

SILVYN® RILL PA 6

SILVYN® RILL PA 12

가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SILVYN® KCLICK-GPZ

UL FILENUMBER E308201

PG

가

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

(RAL 7001)

(RAL 9005), UV

:

PA6

가:

IP 68

IP 69

:

-40°C ~ +115°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® KLICK-GPZ

	PG	Clamping range in mm	SW (mm)	(thread) (mm)	(mm)		SILVYN® RILL	/ PU
SILVYN® KLICK-GPZ								
61801120	7	3 - 6.5	16	8	7	10	10	20
61801130	9	4 - 8	18	8	8	13	13	20
61801140	11	5 - 10	21	8	10	15.8	16	20
61801200	13.5	6 - 11	21	9	11	15.8	16	20
61801202	13.5	6 - 12	24	9	12	18.5	18	20
61801150	16	10 - 14	27	10	14	21.2	21	10
61801160	21	13 - 18	34	11	20	28.5	28	10
61801170	29	18 - 25	40	11	25	34.5	34	10
61801180	36	22 - 32	55	13	32	42.5	42	10
61801190	48	34 - 44	65	14	44	54.5	54	10
SILVYN® KLICK-GPZ								
61801125	7	3 - 6.5	16	8	7	10	10	20
61801135	9	4 - 8	18	8	8	13	13	20
61801145	11	5 - 10	21	8	10	15.8	16	20
61801205	13.5	6 - 11	21	9	11	15.8	16	20
61801215	13.5	6.0 - 12.0	24	9	12	18.5	18	20
61801155	16	10 - 14	27	10	14	21.2	21	10
61801165	21	13 - 18	34	11	20	28.5	28	10
61801175	29	18 - 25	40	11	25	34.5	34	10
61801185	36	22 - 32	55	13	32	42.5	42	10
61801195	48	34 - 44	65	14	44	54.5	54	10