



SILVYN® KLICK NPT

SILVYN® KLICK NPT



가

SILVYN® RILL PA 6

SILVYN® RILL PA 12

UL FILENUMBER E308201

NPT

(24.04.2024)



SILVYN® KCLICK NPT

가

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

(RAL 9005), UV

:

PA6

:

가:

IP 68

IP 69

:

-40°C ~ +115°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® KLICK NPT

	()	mm	(thread) (mm)	(mm)		SILVYN® RILL	/ PU
61800705	NPT 1/4"	34	11.5	7	10.0	10	50
61800715	NPT 3/8"	37	12	10	13.0	13	50
61800725	NPT 3/8"	39	12	12.5	15.8	16	50
61800745	NPT 1/2"	43.5	13	17	21.2	21	50
61800755	NPT 3/4"	47.5	14	21	28.5	28	25
61800765	NPT 1"	52	16	27.5	34.5	34	25
61800775	NPT 1 1/4"	77	18	36.5	42.5	42	25
61800784	NPT 1 1/2"	89	18	42.5	54.5	54	10
61800785	NPT 2"	92	21	48.5	54.5	54	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16