

SILVYN® BRAID PA6

SILVYN® BRAID PA6



가 가

가 가

가

(19.04.2025)



SILVYN® BRAID PA6

6.6 -

ETIM 5:

ETIM 5.0 Class-ID: EC001182

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC001182

ETIM 6.0 Class :

:

:

UL94 V-2

(RAL 9005), UV

:

6.6 -

:

-55°C +125°C

:

가 VAT 가 가 .

(19.04.2025)

©2025 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® BRAID PA6

	()	Clamping range in mm	PU (m)
SILVYN® BRAID PA6			
61721260	6	4 - 10	20
61721261	12	10 - 14	15
61721262	16	14 - 24	15
61721263	20	18 - 26	10
61721264	30	26 - 34	10
61721265	40	32.0 - 42.0	5
SILVYN®BRAID PA6 -			
61721266	6	4.0 - 10.0	750
61721267	12	10.0 - 14.0	500
61721268	16	14.0 - 24.0	400
61721269	20	18.0 - 26.0	250
61721258	30	26.0 - 34.0	250
61721259	40	32.0 - 42.0	250