

SILVYN® MPC 45° M

SILVYN® MPC 45° M - SILVYN® EL/ELU/ELO/ELT



45°

가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® MPC 45° M

SILVYN® EL/ELU/ELO/ELT/ELR ()

UL FILENUMBER E308201

45

ETIM 5: ETIM 5.0 Class-ID: EC001178
ETIM 5.0 Class :

ETIM 6: ETIM 6.0 Class-ID: EC001178
ETIM 6.0 Class :

: IEC EN 61386-23

: (RAL 9005), UV
, RAL 7001

: PA66

가: IP 65 IP 67 + IP

68 (2bar)

: -40°C ~ +120°C

가 VAT 가 가 .



SILVYN® MPC 45° M

		(mm)	SILVYN® EL/ELU/ELO/ELT/ELR	/ PU
SILVYN®MPC 45° M				
55502431	20 x 1.5/1	10.5	16	10
55502432	20 x 1.5/2	14.5	20	10
55502433	25 x 1.5	19	25	10
55502434	32 x 1.5	24.5	32	10
SILVYN®MPC 45° M				
55502435	20 x 1.5/1	10.5	16	10
55502436	20 x 1.5/2	14.5	20	10
55502437	25 x 1.5	19	25	10
55502438	32 x 1.5	24.5	32	10