

SILVYN® MPC

SILVYN® MPC - SILVYN® EL/ELU/ELO/ELT



SILVYN® EL/ELU/ELO/ELT/ELR ()

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® MPC

UL FILENUMBER E308201

PG

6

ETIM 5:

ETIM 5.0 Class-ID: EC001178

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001178

ETIM 6.0 Class :

:

IEC EN 61386-23

:

(RAL 9005), UV
, RAL 7001

:

PA66

가:

IP 65

IP 67 + IP

68 (2bar)

:

-40°C ~ +120°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® MPC

	PG	(mm)	SILVYN® SI	SILVYN® SP/SP-PU	SILVYN® EL/ELU/ELO/ELT/ELR	/ PU
SILVYN® MPC						
55502470	9	9	11 x 14	-	12	10
55502471	11	10.5	13 x 16	12 x 16	16	10
55502472	13.5	10.5	13 x 16	12 x 16	16	10
55502494	13.5	14.5	-	16 x 20	20	10
55502473	16	14.5	-	16 x 20	20	10
55502474	21	19	-	22 x 27	25	10
55502476	29	24.5	-	-	30	10
55502495	29	24.5	-	-	32	10
55502477	36	33	-	-	40	2
55502478	42	39	-	-	50	2
55502479	48	48	-	-	63	1
SILVYN® MPC						
55502496	9	9	11 x 14	-	12	10
55502497	11	10.5	13 x 16	12 x 16	16	10
55502498	13.5	10.5	13 x 16	12 x 16	16	10
55502499	13.5	14.5	-	16 x 20	20	10
55502451	16	14.5	-	16 x 20	20	10
55502452	21	19	-	22 x 27	25	10
55502453	29	24.5	-	-	30	10
55502454	29	24.5	-	-	32	10
55502455	36	33	-	-	40	2
55502456	42	39	-	-	50	2
55502457	48	48	-	-	63	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16