


# SILVYN® FPS

SILVYN® FPS

PVC



SILVYN® MSK-M



SILVYN® USK/USK-M  
IP54



SILVYN® US/US-M + EE-K  
IP54



SILVYN® LKI/LKI-M  
IP54



SILVYN® EE-K



(SILVYN® CHAIN)

-

UL FILENUMBER E308201

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## SILVYN® FPS

PVC  
PVC

PU = 50m ( )

ETIM 5:

ETIM 5.0 Class-ID: EC001177

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001177

ETIM 6.0 Class :

:

IEC EN 61386-23

:

:

가

PVC

:

-25°C ~ +80°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



SILVYN® FPS

|                 | ( ) | ID x OD mm  | (mm) | SILVYN® USK-M/US-M | SILVYN® LKI-M/MSK-M | SILVYN® USK/US/LKI/EE-K | PU ring (m) |
|-----------------|-----|-------------|------|--------------------|---------------------|-------------------------|-------------|
| SILVYN® FPS     |     |             |      |                    |                     |                         |             |
| 61711550        | 10  | 7 x 10      | 8    | 10 x 1,0           | 12 x 1,5            | 7                       | 25          |
| 61711590        | 14  | 10 x 14     | 10   | 12 x 1,5           | 16 x 1,5            | 9                       | 25          |
| 61711630        | 17  | 12.7 x 17.0 | 13   | 16 x 1,5           | 20 x 1,5            | 11                      | 25          |
| 61711670        | 19  | 14.7 x 19.0 | 15   | -                  | -                   | 13,5                    | 25          |
| 61711710        | 21  | 16 x 21     | 17   | 20 x 1,5           | 25 x 1,5            | 16                      | 25          |
| 61711750        | 27  | 21.6 x 27.0 | 20   | 25 x 1,5           | 32 x 1,5            | 21                      | 25          |
| 61711790        | 36  | 29 x 36     | 25   | 32 x 1,5           | 40 x 1,5            | 29                      | 25          |
| 61711830        | 45  | 38 x 45     | 36   | 40 x 1,5           | 50 x 1,5            | 36                      | 25          |
| 61711910        | 56  | 48 x 56     | 40   | 50 x 1,5           | 63 x 1,5            | 48                      | 25          |
| SILVYN® FPS 10M |     |             |      |                    |                     |                         |             |
| 61721690        | 10  | 7 x 10      | 8    | 10 x 1,0           | 12 x 1,5            | 7                       | 10          |
| 61721700        | 14  | 10 x 14     | 10   | 12 x 1,5           | 16 x 1,5            | 9                       | 10          |
| 61721710        | 17  | 12.7 x 17.0 | 13   | 16 x 1,5           | 20 x 1,5            | 11                      | 10          |
| 61721720        | 19  | 14.7 x 19.0 | 15   | -                  | -                   | 13,5                    | 10          |
| 61721730        | 21  | 16 x 21     | 17   | 20 x 1,5           | 25 x 1,5            | 16                      | 10          |
| 61721740        | 27  | 21.6 x 27.0 | 20   | 25 x 1,5           | 32 x 1,5            | 21                      | 10          |
| 61721750        | 36  | 29 x 36     | 25   | 32 x 1,5           | 40 x 1,5            | 29                      | 10          |
| 61721760        | 45  | 38 x 45     | 36   | 40 x 1,5           | 50 x 1,5            | 36                      | 10          |
| 61721780        | 56  | 48 x 56     | 40   | 50 x 1,5           | 63 x 1,5            | 48                      | 10          |