

SILVYN® US EE

SILVYN® US

IP40/IP54/IP66

PG



SILVYN®
FPS
SILVYN® FD-PU

(24.04.2024)



SILVYN® US EE

PG
6

ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class :

:

:

: TPE

가:

IP 54(SILVYN®FPS, FD-PU)

:

-40°C +125°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® US EE

	PG	(mm)	SILVYN® FPS/FD-PU	/ PU
SILVYN® US for SILVYN® FPS / FD-PU				
55502651	7	6	10	50
55502652	9	9	14	50
55502653	11	11.5	17	50
55502654	13.5	13	19	50
55502655	16	14.5	21	50
55502656	21	19.5	27	25
55502657	29	26.5	36	25
55502658	36	36	45	20
55502659	48	45.5	56	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SILVYN® US EE



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16