

SILVYN® US FPS-EDU

SILVYN® US

IP40/IP54/IP66

PG



SILVYN®
FPS-EDU

PG
6

(27.02.2024)



SILVYN® US FPS-EDU

ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class :

:

:

: TPE

가:

IP 54(SILVYN®FPS-EDU)

:

-40°C +125°C

SKINTOP® DIX-M

가

가 VAT 가 가 .

(27.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® US FPS-EDU

| | PG | (mm) | SILVYN® FPS/FD-PU | / PU |
|--------------------------------|----|------|-------------------|------|
| SILVYN® US for SILVYN® FPS-EDU | | | | |
| 55502689 | 9 | 8.5 | 14 | 50 |
| 55502690 | 11 | 11 | 17 | 50 |
| 55502692 | 16 | 14.5 | 21 | 50 |
| 55502693 | 21 | 19.5 | 27 | 25 |
| 55502694 | 29 | 27.5 | 36 | 25 |
| 55502696 | 36 | 35.5 | 45 | 20 |
| 55502697 | 48 | 47 | 56 | 10 |

(27.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16