

SILVYN® US-M FPS-EDU

SILVYN® US-M

IP40/IP54/IP66



SILVYN®
FPS-EDU

(24.04.2024)

SILVYN® US-M FPS-EDU

6

ETIM 5:	ETIM 5.0 Class-ID: EC001180
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC001180
	ETIM 6.0 Class :
:	:
가:	: TPE
	IP 54(SILVYN@FPS-EDU)
:	-40°C +125°C

가 VAT 가 가 .

(24.04.2024)



SILVYN® US-M FPS-EDU

		(mm)	SILVYN® FPS-EDU	/ PU
SILVYN® US-M for SILVYN® FPS-EDU				
55502642	12 x 1.5	8.5	14	50
55502643	16 x 1.5	11	17	50
55502644	20 x 1.5	14.5	21	50
55502645	25 x 1.5	19.5	27	25
55502646	32 x 1.5	27.5	36	25
55502647	40 x 1.5	35	45	20
55502648	50 x 1.5	45	56	10
55502649	63 x 1.5	45	56	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16