

SILVYN® SCH

SILVYN® SCH -



SILVYN® SSV-M/SSVZ-M

SILVYN® SSV/SSV-Z

ETIM 5:

ETIM 5.0 Class-ID: EC000127
ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000127
ETIM 6.0 Class :

가 VAT 가 가 .

(23.04.2024)



SILVYN® SCH

		Clamping range in mm	SILVYN® SI	SILVYN® SP/SP-PU	/ PU
SILVYN® SCH					
52003130	10 - 16 S	10.0 - 16.0	7 x 9 / 9 x 12 / 11 x 14	10 x 14	100
52003140	12 - 20 S	12.0 - 20.0	13 x 16 / 14 x 18	12 x 16	100
52003160	16 - 25 S	16.0 - 25.0	18 x 22	16 x 20	100
52003170	20 - 32 S	20.0 - 32.0	23 x 28	22 x 27	100
52009050	25 - 40 S	25.0 - 40.0	23 x 28 / 32 x 38	30 x 36	100
52009061	35 - 50 S	35.0 - 50.0	32 x 38	38 x 44	50
52009040	40 - 60 S	40.0 - 60.0	-	45 x 51 / 50 x 56	25