

SILVYN® SP-PU

SILVYN® SP-PU - PUR



UV

가

(24.04.2024)



SILVYN® SP-PU

PVC

ETIM 5:

ETIM 5.0 Class-ID: EC001177

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001177

ETIM 6.0 Class :

:

IEC EN 61386-23

:

(RAL 9005), UV

:

PVC PUR

:

UL 94V-0

-20°C +90°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® SP-PU

	ID x OD mm	(mm)	SILVYN® SSV- M/SSVZ-M	SILVYN® USK- M	SILVYN® SSV/SSVZ	SILVYN® USK	SILVYN® SCH	PU ring (m)
SILVYN® SP-PU								
61793620	10.0 x 14.0	50	16 x 1,5/1	12 x 1,5	9/1	9	10 - 16 S	25
61793630	12.0 x 16.0	60	16 x 1,5/2	16 x 1,5	9/2	11	12 - 20 S	25
61793640	14.0 x 18.0	70	20 x 1,5/1	-	11/1	13,5	12 - 20 S	25
61793650	16.0 x 20.0	80	20 x 1,5/2	20 x 1,5	11/2	16	16 - 25 S	25
61793660	22.0 x 27.0	110	25 x 1,5	25 x 1,5	-	21	20 - 32 S	25
61793670	30.0 x 36.0	150	32 x 1,5	32 x 1,5	29/1	29	25 - 40 S	25
61793680	38.0 x 44.0	200	40 x 1,5	40 x 1,5	36	36	32 - 50 S	25

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16