



# SILVYN® FG NM

SILVYN® FG NM



FDA-

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# SILVYN® FG NM

FDA CFR 21 NSF 51 ( )  
ECOLAB®

PVC  
FDA

ETIM 5:

ETIM 5.0 Class-ID: EC001177  
ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001177  
ETIM 6.0 Class :

:

FDA CFR 21  
NSF 51

:

가

:

:

PVC 가 PVC

:

-20°C +60°C  
- : +80 °C

\*

,

가 VAT 가 가 .

(24.04.2024)



SILVYN® FG NM

	( )	ID x OD mm	(mm)	PU ring (m)
SILVYN® FG NM				
55503370	3/8"	12.6 x 17.8	70	30
55503371	1/2"	16.0 x 21.1	100	30
55503372	3/4"	21.0 x 26.4	130	30
55503373	1"	26.5 x 33.1	180	30
55503374	1 1/4"	35.1 x 41.8	225	15
55503375	1 1/2"	40.3 x 47.8	255	15
55503376	2"	51.6 x 59.9	310	15