

# SILVYN® HYGIENIC

SILVYN® HYGIENIC

가 가  
No gaps, voids or outer lying thread - so no risk of contamination of food machines, facilities or components



**CE UK  
CA**



(14.05.2024)

# SILVYN® HYGIENIC



가

DIN EN 1672-2

DIN EN ISO 14159

Security of machinery – Hygienic requirements for the design of machinery

ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class :

:

IEC EN 61386-23

:

: (316 )

:

: 6

:

가:

IP66

IP67

IP68 (2 bar)

IP69

:

-50°C ~ +135°C

가 VAT 가 가 .

(14.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# SILVYN® HYGIENIC

		(mm)		/ PU
SILVYN® HYGIENIC				
55510700	16 x 1.5	10.7	3/8"	1
55510701	20 x 1.5	14.5	1/2"	1
55510702	25 x 1.5	18.7	3/4"	1
55510703	32 x 1.5	24.6	1"	1
55510704	40 x 1.5	32.7	1 1/4"	1
55510705	50 x 1.5	37.7	1 1/2"	1
55510706	63 x 1.5	49	2"	1

(14.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## SILVYN® HYGIENIC



(14.05.2024)