

Cable-Eater

PU (2m)



가

()

UV-

: , , ,

Bunches cable conduit large PUs on a roll, small PUs in bags with Euro-standard holes

ETIM 5:

ETIM 5.0 Class-ID: EC002604

ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC002604

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ETIM 6.0 Class :

:

,UL 94 HB

:

, ,

:

(PP)

:

-30°C to +85°C

가 VAT 가 가 .

	Article description		Bundling area (mm)	Ø (mm)	(mm)		PU (m)
61830302	SHR-08-PPW		6.0 - 9.0	8	0.8	STKP 8	100
61830312	SHR-15-PPW		10.0 - 16.0	15	0.8	STKP 15	50
61830322	SHR-20-PPW		17.0 - 23.0	20	0.9	STKP 20/25	30
61830332	SHR-25-PPW		21.0 - 25.0	25	1	STKP 20/25	20
61830333	SHR-32-PPW		29.0 - 32.0	32	1.3	STKP 32	15
61830300	SHR-08-PPB		6.0 - 9.0	8	0.8	STKP 8	100
61830310	SHR-15-PPB		10.0 - 16.0	15	0.8	STKP 15	50
61830320	SHR-20-PPB		17.0 - 23.0	20	0.9	STKP 20/25	30
61830330	SHR-25-PPB		21.0 - 25.0	25	1	STKP 20/25	20
61830335	SHR-32-PPB		29.0 - 32.0	32	1.3	STKP 32	15
61830390	SHR-08-PPG		6.0 - 9.0	8	0.8	STKP 8	100
61830391	SHR-15-PPG		10.0 - 16.0	15	0.8	STKP 15	50
61830392	SHR-20-PPG		17.0 - 23.0	20	0.9	STKP 20/25	30
61830393	SHR-25-PPG		21.0 - 25.0	25	1	STKP 20/25	20
61830394	SHR-32-PPG		29.0 - 32.0	32	1.3	STKP 32	15
PU							
61830401	SHR-15-PPW 2m		10.0 - 16.0	15	0.8	STKP 15	2
61830402	SHR-20-PPW 2m		17.0 - 23.0	20	0.9	STKP 20/25	2
61830403	SHR-25-PPW 2m		21.0 - 25.0	25	1	STKP 20/25	2
61830396	SHR-15-PPB 2m		10.0 - 16.0	15	0.8	STKP 15	2
61830397	SHR-20-PPB 2m		17.0 - 23.0	20	0.9	STKP 20/25	2
61830398	SHR-25-PPB 2m		21.0 - 25.0	25	1	STKP 20/25	2
61830406	SHR-15-PPG 2m		10.0 - 16.0	15	0.8	STKP 15	2
61830407	SHR-20-PPG 2m		17.0 - 23.0	20	0.9	STKP 20/25	2
61830408	SHR-25-PPG 2m		21.0 - 25.0	25	1	STKP 20/25	2

©2024 Lapp Group - all rights reserved.

(24.04.2024)

http://lappkorea.lappgroup.com

data sheet

PN 0456 / 02_03_16