

/

/



M6 M8

UL E501239:

- :
- PVC-
-
-
-
-

ETIM 5:

ETIM 6:

:
:

ETIM 5.0 Class-ID: EC000490
ETIM 5.0 :

ETIM 6.0 Class-ID: EC000490
ETIM 6.0 Class :

Assembled ground straps
Green/Yellow

IEC 60 228 class 6

(25.04.2024)

/

IEC 60 228 class 6
가

:
Assembled ground straps
7 x outer diameter
Assembled flat ground straps
2 x thickness of the strap

:
2500 V

:
-30°C +70°C

-5°C +70°C

가 VAT 가 가 . 가 가 . (.) 가 .
가 가 .

		UL	Cross-section (mm ²)		(mm)	Thickness (mm) +- 0,5 mm	kg/1.000 pieces	PU
4571120	Ground strap 1 x 4/M6/170 mm GN/YE	no	4	M6	170	-	6.5	25
4571123	Ground strap 1x4/M8/300mm GN/YE	no	4	M8	300	-	11.4	25
4571121	Ground straps 1x16/M6/170mm GN/YE	no	16	M6	170	-	26.2	25
4571198	Erdungsband 1x16/M6/500mm GN/YE	no	16	M6	500	-	76.8	25
4571124	Ground strap 1x16/M8/300mm GN/YE	no	16	M8	300	-	46.2	25
4571122	Ground strap 1x25/M6/170mm GN/YE	no	25	M6	170	-	40.8	25
4571125	Ground strap 1x25/M8/300mm GN/YE	no	25	M8	300	-	72	25
-								
4571132	Flat ground strap/press. 1X10/M6/200mm	no	10	M6	200	1	18	25
4571135	Flat ground strap/press. 1x10/M6/300mm	no	10	M6	300	1	27	25
70399965	Flachband-Erder/Press. 1X16/M6/200mm	no	16	M6	200	1.5	30.72	25
70399966	Flachband-Erder/Press. 1X16/M6/300mm	no	16	M6	300	1.5	46.08	25
4571133	Flat ground strap/press. 1x16/M8/200mm	no	16	M8	200	1.5	29	25
4571136	Flat ground strap/press. 1x16/M8/300mm	no	16	M8	300	1.5	43.5	25

/

		UL	Cross-section (mm ²)		(mm)	Thickness (mm) +- 0,5 mm	kg/1.000 pieces	PU
4571134	Flat ground strap/press. 1X25/M8/200mm	no	25	M8	200	1.5	45	25
4571137	Flat ground strap/press. 1x25/M8/300mm	no	25	M8	300	1.5	71.11	25
70399969	Flachband-Erder/Press. 1X25/M8/500mm	no	25	M8	500	1.5	120	25
4571196	Flachband-Erder/Hülse 1x6/M6/200mm	yes	6	M6	200	2	15	25
4571197	Flachband-Erder/Hülse 1x6/M6/300mm	yes	6	M6	300	2	20	25
4571126	Flat ground strap/sleeves 1x10/M6/200mm	yes	10	M6	200	2.5	25	25
4571129	Flat ground strap/sleeves 1x10/M6/300mm	yes	10	M6	300	2.5	32	25
4571127	Flat ground strap/sleeves 1x16/M8/200mm	yes	16	M8	200	3	35	25
4571130	Flat ground strap/sleeves 1x16/M8/300mm	yes	16	M8	300	3	51	25
4571128	Flat ground strap/sleeves 1x25/M8/200mm	yes	25	M8	200	3.5	55	25
4571131	Flat ground strap/sleeves 1x25/M8/300mm	yes	25	M8	300	3.5	80	25

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16