

UV-stabilised cable ties with steel nose

가 , , UV



가 : , ,
Lock (16)

2%

UL file number TY-RAP®: E49405, see table

UL94 V-2

가 "B"(: TYB 24M)가 가

(23.04.2024)

UV-stabilised cable ties with steel nose

ETIM 5:	ETIM 5.0 Class-ID: EC000046
	ETIM 5.0 :
ETIM 6:	ETIM 6.0 Class-ID: EC000046
	ETIM 6.0 Class :
:	Black (RAL 9005), UV-resistant
:	6.6
:	-40°C +85°C

B = , 가
TY-RAP® Thomas & Betts

가 VAT 가 가 .

UV-stabilised cable ties with steel nose

	Article description	UL	x (mm)	Bundling Ø (mm)	(N)	/ PU
Black (UV-resistant)						
61723010	TYB* 23 MX	yes	92.0 x 2.3	2 - 16	80	1000
61723110	TY 232 MX	yes	203.0 x 2.3	2 - 50	80	1000
61723120	TY 234 MX	yes	356.0 x 2.3	2 - 102	80	1000
61723020	TYB* 24 MX	yes	140.0 x 3.6	2 - 29	133	1000
61723130	TY 242 MX	yes	208.0 x 3.6	2 - 50	180	1000
61723040	TY 26 MX	yes	284.0 x 3.6	2 - 76	180	1000
61723140	TY 244 MX	yes	368.0 x 3.6	2 - 103	180	1000
61723030	TYB* 25 MX	yes	186.0 x 4.8	3.5 - 45	220	1000
61723150	TY 253 MX	yes	290.0 x 4.8	3.5 - 78	220	1000
61723060	TY 28 MX	yes	361.0 x 4.8	3.5 - 102	220	1000
61723160	TY 272 MX	yes	223.0 x 6.9	6 - 50	540	500
61723050	TY 27 MX	yes	340.0 x 7.0	6 - 90	540	500
61723070	TY 29 MX	yes	771.0 x 6.9	6 - 229	540	500

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16