

EKK single clamp

EKK



ÖLFLEX® 가 -LIFT RH RS
: 800 N (80 kg)

T5

가

ETIM 5:

ETIM 5.0 Class-ID: EC000127
ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000127
ETIM 6.0 Class :

:

High mechanical load: +65°C
Low mechanical load: +100°C

가 VAT 가 가 .

(24.04.2024)



EKK single clamp

		Ø (mm)	x x (mm)	(kg/)	/ PU
52026000	EKK 18	15.0 - 18.0	125.0 x 45.0 x 120.0	1.4	1
52026011	EKK 26	19.0 - 26.0	125.0 x 45.0 x 120.0	1.4	1