


KB

DIN 46234



()

2,5 6

BUS

VG 88710

Coil form DIN 46234 (versions mit * are not according to DIN 46234)

ETIM 5:

ETIM 5.0 Class-ID: EC001052

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC001052

ETIM 6.0 Class :

:

s =

:

:

+120°C

*

가

VAT

가

가

.

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

		mm ²	UL	d1	d3	l1	a1		/ PU
63204015	KB1-2,5R DIN 46234	0.5 - 1.5	no	2.7	6	11	5	PEW 12.1071	100
63204025	KB1-3R DIN 46234	0.5 - 1.5	no	3.2	6	11	5	PEW 12.1071	100
63204035	KB1-3,5R DIN 46234	0.5 - 1.5	no	3.7	6	11	5	PEW 12.1071	100
63204045	KB1-4R DIN 46234	0.5 - 1.5	no	4.3	8	12	5	PEW 12.1071	100
63204055	KB1-5R DIN 46234	0.5 - 1.5	no	5.3	10	13	5	PEW 12.1071	100
63204065	KB1-6R*	0.5 - 1.5	no	6.5	11	14	5	PEW 12.1071	100
63204075	KB1-8R*	0.5 - 1.5	no	8.4	14	17	5	PEW 12.1071	100
63204085	KB1-10R*	0.5 - 1.5	no	10.5	18	19	5	PEW 12.1071	100
63204095	KB2,5-3R DIN 46234	1.5 - 2.5	no	3.2	6	11	5	PEW 12.1071	100
63204105	KB2,5-3,5R DIN 46234	1.5 - 2.5	no	3.7	6	11	5	PEW 12.1071	100
63204115	KB2,5-4R DIN 46234	1.5 - 2.5	no	4.3	8	12	5	PEW 12.1071	100
63204125	KB2,5-5R*	1.5 - 2.5	no	5.3	10.1	14	5	PEW 12.1071	100
63204135	KB2,5-6R DIN 46234	1.5 - 2.5	no	6.5	11	16	5	PEW 12.1071	100
63204145	KB2,5-8R DIN 46234	1.5 - 2.5	no	8.4	14	17	5	PEW 12.1071	100
63204155	KB2,5-10R*	1.5 - 2.5	no	10.5	18	19	5	PEW 12.1071	100
63204165	KB2,5-12R*	1.5 - 2.5	no	13	19.8	15	5	PEW 12.1071	100
63204175	KB6-4R*	2.5 - 6	no	4.3	8	14	6	PEW 12.1071	100
63204185	KB6-5R*	2.5 - 6	no	5.3	10.1	15	6	PEW 12.1071	100
63204195	KB6-6R*	2.5 - 6	no	6.5	11.1	16	6	PEW 12.1071	100
63204205	KB6-8R*	2.5 - 6	no	8.4	14.1	19	6	PEW 12.1071	100
63204215	KB6-10R DIN 46234	2.5 - 6	no	10.5	18	21	6	PEW 12.1071	100
63204225	KB6-12R*	2.5 - 6	no	13	19	23	6	PEW 12.1071	100
63204235	KB10-5R DIN 46234	10	no	5.3	10	16	8	PEW 12.1071	100
63204245	KB10-6R DIN 46234	10	no	6.5	11	17	8	PEW 12.1071	100

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

		mm ²	UL	d1	d3	l1	a1		/ PU
63204255	KB10-8R DIN 46234	10	no	8.4	14	20	8	PEW 12.1071	100
63204265	KB10-10R DIN 46234	10	no	10.5	18	21	8	PEW 12.1071	100
63204275	KB10-12R DIN 46234	10	no	13	22	23	8	PEW 12.1071	100
63204285	KB16-5R DIN 46234	16	no	5.3	11	20	10	PEW 12.033	100
63204295	KB16-6R DIN 46234	16	no	6.5	11	20	10	PEW 12.033	100
63204305	KB16-8R DIN 46234	16	no	8.4	14	22	10	PEW 12.033	100
63204315	KB16-10R DIN 46234	16	no	10.5	18	24	10	PEW 12.033	100
63204325	KB16-12R DIN 46234	16	no	13	22	26	10	PEW 12.033	100
63204335	KB25-5R DIN 46234	25	no	5.3	12	25	11	PEW 12.033	100
63204345	KB25-6R DIN 46234	25	no	6.5	12	25	11	PEW 12.033	100
63204355	KB25-8R DIN 46234	25	no	8.4	16	25	11	PEW 12.033	100
63204365	KB25-10R DIN 46234	25	no	10.5	18	26	11	PEW 12.033	100
63204375	KB25-12R DIN 46234	25	no	13	22	31	11	PEW 12.033	100
63204385	KB25-16R DIN 46234	25	no	17	28	35	11	PEW 12.033	100
63204395	KB35-6R DIN 46234	35	no	6.5	15	26	12	-	100
63204405	KB35-8R DIN 46234	35	no	8.4	16	26	12	-	100
63204415	KB35-10R DIN 46234	35	no	10.5	18	27	12	-	100
63204425	KB35-12R DIN 46234	35	no	13	22	31	12	-	100
63204445	KB50-6R DIN 46234	50	no	6.5	18	34	16	-	100
63204455	KB50-8R DIN 46234	50	no	8.4	18	34	16	-	100

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

KB

		mm ²	UL	d1	d3	l1	a1		/ PU
63204465	KB50-10R DIN 46234	50	no	10.5	18	34	16	-	100
63204475	KB50-12R DIN 46234	50	no	13	22	36	16	-	100
63204485	KB50-16R DIN 46234	50	no	17	28	40	16	-	100
63204495	KB70-6R DIN 46234	70	no	6.5	22	38	18	-	100
63204505	KB70-8R DIN 46234	70	no	8.4	22	38	18	-	100
63204515	KB70-10R DIN 46234	70	no	10.5	22	38	18	-	100
63204525	KB70-12R DIN 46234	70	no	13	22	38	18	-	100
63204535	KB70-16R DIN 46234	70	no	17	28	42	18	-	100
63204545	KB95-8R DIN 46234	95	no	8.4	24	42	20	-	50
63204555	KB95-10R DIN 46234	95	no	10.5	24	42	20	-	50
63204565	KB95-12R DIN 46234	95	no	13	24	42	20	-	50
63204575	KB95-16R DIN 46234	95	no	17	28	44	20	-	50
63204585	KB120-8R DIN 46234	120	no	8.4	24	44	22	-	25
63204595	KB120-10R DIN 46234	120	no	10.5	24	44	22	-	25
63204605	KB120-12R DIN 46234	120	no	13	24	44	22	-	25
63204615	KB120-16R*	120	no	17	28	44	22	-	25
63204625	KB150-10R DIN 46234	150	no	10.5	30	50	24	-	25
63204635	KB150-12R DIN 46234	150	no	13	30	50	24	-	25
63204645	KB150-16R DIN 46234	150	no	17	30	50	24	-	25
63204655	KB185-10R DIN 46234	185	no	10.5	36	50	28	-	20
63204665	KB185-12R DIN	185	no	13	36	50	28	-	20

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

		mm ²	UL	d1	d3	l1	a1		/ PU
	46234								
63204675	KB185-16R DIN 46234	185	no	17	36	50	28	-	20
63204685	KB240-10R DIN 46234	240	no	10.5	38	56	32	-	10
63204695	KB240-12R DIN 46234	240	no	13	38	56	32	-	10
63204705	KB240-16R DIN 46234	240	no	17	38	56	32	-	10

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16