

AHI

DIN



DIN 46228, part 4 (0.25 mm² 0.34 mm²)

AHI I (): 30 x 0.25 - 6 mm LBU, 30 x 0.34 - 6 mm TQ, 30 x 0.5 - 8 mm ON, 30 x 0.75 - 8 mm WH, 30 x 1.00 - 8 mm YE
 AHI II (): 50 x 0.5 - 8 mm OG, 100 x 0.75 - 8 mm WH, 100 x 1.00 - 8 mm YE, 100 x 1.5 - 8 mm RD, 50 x 2.5 - 8 mm BU
 AHI III (): 50 x 4.00 - 10 mm GY, 20 x 6.0 - 12 mm BK, 20 x 10.00 - 12 mm WH, 10 x 16.00 - 12 mm GN

ETIM 5: ETIM 5.0 Class-ID: EC000524
 ETIM 5.0 class :
 ETIM 6: ETIM 6.0 Class-ID: EC000524
 ETIM 6.0 Class :

가 VAT 가 가 .



AHI

		mm ²		()	PU
AHI					
61794720	AHI I	0.25 - 1	PEW 12.090	150 x 1	1
61794730	AHI II	0.5 - 2.5	PEW 12.090	400 x 1	1
61794740	AHI III	4 - 16	PEW 12.090 / PEW 12.091	100 x 1	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16