

DIN assorted boxes conductor end sleeves

DIN

가

가



DIN 46228, part 4 (0.25 mm² 0.34 mm²)

DIN I:

30x0.25 - 6mm BU, 30x0.34 - 6mm YE, 30x0.5 - 8mm WH, 30x0.75 - 8mm GY, 30x1.00 - 8mm RD

DIN II:

50 x 0.5 - 8 mm WH, 100 x 0.75 - 8 mm GY, 100 x 1.00 - 8 mm RD, 100 x 1.5 - 8 mm BK, 50 x 2.5 - 8 mm BU

DIN III:

40 x 4.00 - 10 mm GY, 20 x 6.0 - 12 mm YE, 20 x 10.00 - 12 mm RD, 10 x 16.00 - 12 mm BU

ETIM 5:

ETIM 5.0 Class-ID: EC000524

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000524

ETIM 6.0 Class :

가 VAT

가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

DIN assorted boxes conductor end sleeves

		mm ²		()	PU
DIN assortment box					
61802040	DIN I	0.25 - 1	PEW 12.090	150 x 1	1
61802041	DIN II	0.5 - 2.5	PEW 12.090	400 x 1	1
61802042	DIN III	4 - 16	PEW 12.090 / PEW 12.091	100 x 1	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16