

PEW 12

Crimping inserts for PEW 12 for pressing end sleeves, insulated and uninsulated connectors und screen connectors



Product code is engraved on the upper and on the lower part of the die set
가

High flexibility: Interchangeable inserts that fit into either the PEW 12 / PEW 12S manual crimping tool, the E-PEW 12 electric crimping tool or the CM 25-1 crimping machine (compatibility see datasheet)

Crimping dies are delivered without tool

ETIM 5:

ETIM 5.0 Class-ID: EC001282

ETIM 5.0 class : ,

ETIM 6:

ETIM 6.0 Class-ID: EC001282

ETIM 6.0 Class : / ,

가 VAT 가 가 .

(23.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

PEW 12

			(mm ²)	(mm)	Ø (mm)		() Ø (mm)	/ PU
61813802	PEW 12.090	-	0,25 - 6	-	-		-	1
61813803	PEW 12.091	-	10.0 - 25.0	-	-	w-	-	1
61813993	PEW 12.331	-	35.0 - 50.0	-	-	w-	-	1
61813911	PEW 12S.093	-	70	-	-	w-	-	1
61813912	PEW 12S.094	-	95	-	-	w-	-	1
61813913	PEW 12.090-6	-	-	-	-		-	1
61815642	PEW 12.097	-	-	-	-	w-	-	1
61813914	PEW 12.064	-	-	-	-	ISO	-	1
61813812	PEW 12.060	-	0.5 - 6.0	-	-	ISO	-	1
61813916	PEW 12.1071	-	0.5 - 10	-	-	w-	-	1
61813862	PEW 12.033	-	16 - 25	-	-		-	1
61814600	PEW 12.045	2.8 + 4.8	0.1 - 2.5	-	-		-	1
61814601	PEW 12.045 Locator	2.8 + 4.8	0.1 - 2.5	-	-	-	-	1
61813991	PEW 12.838	-	-	-	-		-	1
61813992	PEW 12.838 Locator	-	0,75 - 1,5	-	-	-	-	1
61813808	PEW 12.050	4.8 + 6.3	0.5 - 6.0	-	-		-	1
61813890	PEW 12.050 Locator	4.8 + 6.3	0.5 - 6.0	-	-	-	-	-
61813809	PEW 12.050-014 Locator	-	1 - 2,5	-	-	-	-	1
61815645	PEW 12.465	-	1 - 2,5	-	-		-	1
61815646	PEW 12.465 Locator	-	-	-	-	-	-	1
61815643	PEW 12.751	-	-	-	-		-	1
61815644	PEW 12.751 Locator	-	-	-	-	-	-	1
61815647	PEW 12 Universal positioning aid	-	-	-	-	-	-	1
One piece screen connectors RSK (suitable for PEW 12 tool)								
61815635	PEW 12.1448/101 A	RSK 5101	-	-	-	-	1.27 - 1.79	1
61815636	PEW 12.1449/101 B	RSK 5101	-	-	-	-	1.8 - 2.28	1

(23.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

PEW 12

			(mm ²)	(mm)	Ø (mm)		() Ø (mm)	/ PU
61815637	PEW 12.1450/201 C	RSK 5201	-	-	-	-	2.29 - 2.55	1
61815638	PEW 12.1341/201 D	RSK 5201	-	-	-	-	2.56 - 3.0	1
61815639	PEW 12.1451/201 E	RSK 5201	-	-	-	-	3.01 - 3.34	1
61815640	PEW 12.1452/201 F	RSK 5201	-	-	-	-	3.35 - 3.65	1
61815641	PEW 12.1453/301 G	RSK 5301	-	-	-	-	3.66 - 4.13	1
61813869	PEW 12.374/301 H	RSK 5301	-	-	-	-	4.14 - 4.71	1
61813868	PEW 12.373/301 J	RSK 5301	-	-	-	-	4.72 - 5.12	1
61813864	PEW 12.599/401 K	RSK 5401	-	-	-	-	5.13 - 5.86	1
61813865	PEW 12.375/401 L	RSK 5401	-	-	-	-	5.87 - 6.36	1
61813866	PEW 12.354/401 M	RSK 5401	-	-	-	-	6.37 - 7.0	1
61813867	PEW 12.619/401 N	RSK 5401	-	-	-	-	7.01 - 7.62	1
Two-part screen connectors SHIELD-KON® (suitable for PEW 12 tool)								
61813881	PEW 12.1425 SK	GSC 101 / 128 / 149 / 156 / 175	-	-	-	-	-	1
61813882	PEW 12.1426 SK	GSC 187 / 194 / 199 / 205 / 219 / 225 / 232	-	-	-	-	-	1
61813883	PEW 12.1427 SK	GSC 261 / 275 / 281 / 287 / 297	-	-	-	-	-	1
61813884	PEW 12.1428 SK	GSC 312 / 327 / 348	-	-	-	-	-	1
61813885	PEW 12.1429 SK	GSC 359 / 375	-	-	-	-	-	1
61813886	PEW 12.1430 SK	GSC 405 / 415 / 425	-	-	-	-	-	1
61813887	PEW 12S.1440 SK	GSC 460 / 500	-	-	-	-	-	1
Coax connectors (suitable for PEW 12 tool)								
61813813	PEW 12.100	-	-	5.4/6.48/1.72	6.4/7.6/2.1	-	-	1
61813814	PEW 12.110	-	RG 174, 58	5.4/4.52/1.72	6.4/5.4/2.1	-	-	1
61813827	PEW 12.111	-	-	8.23/6.48/1.72/1.07	9.4/7.6/2.1/1.3	-	-	1

(23.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

PEW 12

			(mm ²)	(mm)	Ø (mm)		() Ø (mm)	/ PU
61813816	PEW 12.114	-	-	10.9/2.54	12.0/3.0		-	1
61813818	PEW 12.119	-	-	1.75/9.73	2.1/10.7		-	1
61813852	PEW 12.158	-	-	7.0/8.4/8.1	7.7/9.5/9.5		-	1
61813853	PEW 12.159	-	-	3.25/4.52/5.4/1.72/ 1.07/0.72	3.9/5.4/6.4/2.1/1.3/ 0.95		-	1
61813861	PEW 12.772	-	-	2.67/3.25/3.83	3.1/3.8/4.2		-	1
Other connectors (suitable for PEW 12 tool)								
61813849	PEW 12.155	-	-	4.20/3.65/5.0	5.4/4.3/6.0		-	1
61813825	PEW 12.031	-	1.5 - 10.0	-	-		-	1
61813811	PEW 12.032	-	0.5 - 10	-	-		-	1
61813823	PEW 12.020	-	0,5 - 2,5	-	-		-	1
61813824	PEW 12.030	-	4.0 - 10.0	-	-	w-	-	1
61813826	PEW 12.063	-	10.0 - 16.0	-	-		-	1
61813804	PEW 12.092	-	35.0 - 50.0	-	-	w-	-	1
61814605	PEW 12.691	-	0.5 - 6.0	-	-	ISO	-	1
61814606	PEW 12.742	-	0,5 - 2,5	-	-		-	1
61814607	PEW 12.745	-	1.25-6	-	-		-	1