

PEW 12

Crimping inserts for PEW 12 for pressing end sleeves, insulated and uninsulated connectors und screen connectors



Product code is engraved on the upper and on the lower part of the die set
가

High flexibility: Interchangeable inserts that fit into either the PEW 12 / PEW 12S manual crimping tool, the E-PEW 12 electric crimping tool or the CM 25-1 crimping machine (compatibility see datasheet)

Crimping dies are delivered without tool

ETIM 5:

ETIM 5.0 Class-ID: EC001282

ETIM 5.0 class : ,

ETIM 6:

ETIM 6.0 Class-ID: EC001282

ETIM 6.0 Class : / ,

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

| | | | (mm ²) | (mm) | Ø (mm) | | () Ø (mm) | / PU |
|--|-------------------------------------|-----------|--------------------|------|-----------|-----|---------------|------|
| 61813802 | PEW 12.090 | - | 0,25 - 6 | - | - | | - | 1 |
| 61813803 | PEW 12.091 | - | 10.0 - 25.0 | - | - | w- | - | 1 |
| 61813993 | PEW 12.331 | - | 35.0 - 50.0 | - | - | w- | - | 1 |
| 61813911 | PEW 12S.093 | - | 70 | - | - | w- | - | 1 |
| 61813912 | PEW 12S.094 | - | 95 | - | - | w- | - | 1 |
| 61813913 | PEW 12.090-6 | - | - | - | - | | - | 1 |
| 61815642 | PEW 12.097 | - | - | - | - | w- | - | 1 |
| 61813914 | PEW 12.064 | - | - | - | - | ISO | - | 1 |
| 61813812 | PEW 12.060 | - | 0.5 - 6.0 | - | - | ISO | - | 1 |
| 61813916 | PEW 12.1071 | - | 0.5 - 10 | - | - | w- | - | 1 |
| 61813862 | PEW 12.033 | - | 16 - 25 | - | - | | - | 1 |
| 61814600 | PEW 12.045 | 2.8 + 4.8 | 0.1 - 2.5 | - | - | | - | 1 |
| 61814601 | PEW 12.045 Locator | 2.8 + 4.8 | 0.1 - 2.5 | - | - | - | - | 1 |
| 61813991 | PEW 12.838 | - | - | - | - | | - | 1 |
| 61813992 | PEW 12.838 Locator | - | 0,75 - 1,5 | - | - | - | - | 1 |
| 61813808 | PEW 12.050 | 4.8 + 6.3 | 0.5 - 6.0 | - | - | | - | 1 |
| 61813890 | PEW 12.050 Locator | 4.8 + 6.3 | 0.5 - 6.0 | - | - | - | - | - |
| 61813809 | PEW 12.050-014 Locator | - | 1 - 2,5 | - | - | - | - | 1 |
| 61815645 | PEW 12.465 | - | 1 - 2,5 | - | - | | - | 1 |
| 61815646 | PEW 12.465 Locator | - | - | - | - | - | - | 1 |
| 61815643 | PEW 12.751 | - | - | - | - | | - | 1 |
| 61815644 | PEW 12.751 Locator | - | - | - | - | - | - | 1 |
| 61815647 | PEW 12 Universal positioning aid | - | - | - | - | - | - | 1 |
| One piece screen connectors RSK (suitable for PEW 12 tool) | | | | | | | | |
| 61815635 | PEW 12.1448/101 A | RSK 5101 | - | - | - | - | 1.27 - 1.79 | 1 |
| 61815636 | PEW 12.1449/101 B | RSK 5101 | - | - | - | - | 1.8 - 2.28 | 1 |
| | | | | | | | | |

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

| | | | (mm ²) | (mm) | ∅ (mm) | () ∅ (mm) | / PU |
|--|-------------------|---|--------------------|---------------------|-----------------|---------------|------|
| 61815637 | PEW 12.1450/201 C | RSK 5201 | - | - | - | 2.29 - 2.55 | 1 |
| 61815638 | PEW 12.1341/201 D | RSK 5201 | - | - | - | 2.56 - 3.0 | 1 |
| 61815639 | PEW 12.1451/201 E | RSK 5201 | - | - | - | 3.01 - 3.34 | 1 |
| 61815640 | PEW 12.1452/201 F | RSK 5201 | - | - | - | 3.35 - 3.65 | 1 |
| 61815641 | PEW 12.1453/301 G | RSK 5301 | - | - | - | 3.66 - 4.13 | 1 |
| 61813869 | PEW 12.374/301 H | RSK 5301 | - | - | - | 4.14 - 4.71 | 1 |
| 61813868 | PEW 12.373/301 J | RSK 5301 | - | - | - | 4.72 - 5.12 | 1 |
| 61813864 | PEW 12.599/401 K | RSK 5401 | - | - | - | 5.13 - 5.86 | 1 |
| 61813865 | PEW 12.375/401 L | RSK 5401 | - | - | - | 5.87 - 6.36 | 1 |
| 61813866 | PEW 12.354/401 M | RSK 5401 | - | - | - | 6.37 - 7.0 | 1 |
| 61813867 | PEW 12.619/401 N | RSK 5401 | - | - | - | 7.01 - 7.62 | 1 |
| Two-part screen connectors SHIELD-KON® (suitable for PEW 12 tool) | | | | | | | |
| 61813881 | PEW 12.1425 SK | GSC 101 / 128 / 149 / 156 / 175 | - | - | - | - | 1 |
| 61813882 | PEW 12.1426 SK | GSC 187 / 194 / 199 / 205 / 219 / 225 / 232 | - | - | - | - | 1 |
| 61813883 | PEW 12.1427 SK | GSC 261 / 275 / 281 / 287 / 297 | - | - | - | - | 1 |
| 61813884 | PEW 12.1428 SK | GSC 312 / 327 / 348 | - | - | - | - | 1 |
| 61813885 | PEW 12.1429 SK | GSC 359 / 375 | - | - | - | - | 1 |
| 61813886 | PEW 12.1430 SK | GSC 405 / 415 / 425 | - | - | - | - | 1 |
| 61813887 | PEW 12S.1440 SK | GSC 460 / 500 | - | - | - | - | 1 |
| Coax connectors (suitable for PEW 12 tool) | | | | | | | |
| 61813813 | PEW 12.100 | - | - | 5.4/6.48/1.72 | 6.4/7.6/2.1 | - | 1 |
| 61813814 | PEW 12.110 | - | RG 174, 58 | 5.4/4.52/1.72 | 6.4/5.4/2.1 | - | 1 |
| 61813827 | PEW 12.111 | - | - | 8.23/6.48/1.72/1.07 | 9.4/7.6/2.1/1.3 | - | 1 |

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

PEW 12

| | | | (mm ²) | (mm) | Ø (mm) | | () Ø (mm) | / PU |
|---|------------|---|--------------------|----------------------------------|------------------------------|-----|---------------|------|
| 61813816 | PEW 12.114 | - | - | 10.9/2.54 | 12.0/3.0 | | - | 1 |
| 61813818 | PEW 12.119 | - | - | 1.75/9.73 | 2.1/10.7 | | - | 1 |
| 61813852 | PEW 12.158 | - | - | 7.0/8.4/8.1 | 7.7/9.5/9.5 | | - | 1 |
| 61813853 | PEW 12.159 | - | - | 3.25/4.52/5.4/1.72/ 1.07/0.72 | 3.9/5.4/6.4/2.1/1.3/ 0.95 | | - | 1 |
| 61813861 | PEW 12.772 | - | - | 2.67/3.25/3.83 | 3.1/3.8/4.2 | | - | 1 |
| Other connectors (suitable for PEW 12 tool) | | | | | | | | |
| 61813849 | PEW 12.155 | - | - | 4.20/3.65/5.0 | 5.4/4.3/6.0 | | - | 1 |
| 61813825 | PEW 12.031 | - | 1.5 - 10.0 | - | - | | - | 1 |
| 61813811 | PEW 12.032 | - | 0.5 - 10 | - | - | | - | 1 |
| 61813823 | PEW 12.020 | - | 0,5 - 2,5 | - | - | | - | 1 |
| 61813824 | PEW 12.030 | - | 4.0 - 10.0 | - | - | w- | - | 1 |
| 61813826 | PEW 12.063 | - | 10.0 - 16.0 | - | - | | - | 1 |
| 61813804 | PEW 12.092 | - | 35.0 - 50.0 | - | - | w- | - | 1 |
| 61814605 | PEW 12.691 | - | 0.5 - 6.0 | - | - | ISO | - | 1 |
| 61814606 | PEW 12.742 | - | 0,5 - 2,5 | - | - | | - | 1 |
| 61814607 | PEW 12.745 | - | 1.25-6 | - | - | | - | 1 |

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16