

HOTY

HOTY

- PVC
UV

2 : 1

가



-가
UV

, UL94 VO

: . +18°C

ETIM 5:

ETIM 5.0 Class-ID: EC000217

ETIM 5.0 Class-Description: Schrumpfschlauch

ETIM 6:

ETIM 6.0 Class-ID: EC000217

ETIM 6.0 Class :

:

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



HOTY

	Article description	Ø (mm)	(mm)	, +- 0.1 mm	PU (m)
61716700	HOTY 1	2.5	2.5 - 1.2	0.45	100
61716720	HOTY 2	4	4 - 2	0.5	100
61716740	HOTY 3	6	6 - 3	0.5	100
61716760	HOTY 4	7	7 - 4	0.5	100
61716780	HOTY 6	11	11 - 6	0.6	100
61716800	HOTY 8	14	14 - 8	0.6	100
61716820	HOTY 10	17	17 - 10	0.8	100
61716840	HOTY 13	20	20 - 13	1.0	100
61716860	HOTY 16	25	25 - 16	1.0	50
61716880	HOTY 20	31	31 - 20	1.0	50

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16