

PROTECT-M/PROTECT-T

TBW / TBM

3 : 1 /

/



600 V, 90°C

UV-
Halogen-free

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

PROTECT-M/PROTECT-T

1.0 m

ETIM 5:	ETIM 5.0 Class-ID: EC000217
	ETIM 5.0 Class-Description: Schrumpfschlauch
ETIM 6:	ETIM 6.0 Class-ID: EC000217
	ETIM 6.0 Class :
:	PROTECT-M: medium wall
	PROTECT-T: heavy wall
	: 15 kV/mm
:	: 3:1
:	
:	가 가
:	-40°C ~ +120°C
	: +110°C

가 VAT 가 가 .

(25.04.2024)



PROTECT-M/PROTECT-T

	Article description	(mm)	, +- 0.1 mm	PU (m)	PU
61742460	PROTECT-M 12/3 BK	12 - 3	2.2	15	1
61742461	PROTECT-M 33/8 BK	33 - 8	2.6	10	1
61742462	PROTECT-M 40/12 BK	40 - 12	2.6	5	1
61742463	PROTECT-M 56/17 BK	56 - 17	2.9	3	1
61742464	PROTECT-M 92/26 BK	92 - 26	3.15	1	1
61742455	PROTECT-T 13/3 BK	13.0 - 3.0	2.65	25	1
61742456	PROTECT-T 19/6 BK	19 - 6	2.65	15	1
61742457	PROTECT-T 45/13 BK	45 - 13	3.7	5	1
61742458	PROTECT-T 52/15 BK	52.0 - 15.0	4.1	3	1
61742459	PROTECT-T 130/45 BK	130 - 45	4.2	1	1

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16