

# Temflex™ 1500 insulating tape

Temflex™ 1500- PVC

VDE



PVC

VDE : 5

ETIM 5:

ETIM 5.0 Class-ID: EC000128  
ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000128  
ETIM 6.0 Class :

:

: 170%  
: 20N/10mm

:

: 0.15mm

:

PVC

:

: 40kV/mm

(24.04.2024)



# Temflex™ 1500 insulating tape

:

0°C ~ +90°C

Temflex™ 1183 3M

가 VAT 가 가 .

(24.04.2024)



# Temflex™ 1500 insulating tape

			(m) x (mm)	(mm) x		/ PU
61721040	Temflex	1015		10.0 x 15.0 x 0.15	PVC	10
61721030	Temflex	1015		10.0 x 15.0 x 0.15	PVC	10
61721050	Temflex	1015		10.0 x 15.0 x 0.15	PVC	10
61721060	Temflex	1015		10.0 x 15.0 x 0.15	PVC	10
61721070	Temflex	1015		10.0 x 15.0 x 0.15	PVC	10
61721080	Temflex	1015	/	10.0 x 15.0 x 0.15	PVC	10
61721045	Temflex	1015		10.0 x 15.0 x 0.15	PVC	10
61721090	Temflex	2515		25.0 x 15.0 x 0.15	PVC	10
61721120	Temflex	2515		25.0 x 15.0 x 0.15	PVC	10
61721130	Temflex	2515		25.0 x 15.0 x 0.15	PVC	10
61721140	Temflex	2525		25.0 x 25.0 x 0.15	PVC	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16