

EPIC® DATA M12X

The M12X data connector transmits data and signals with absolute reliability. Thanks to its vibration-proof design, it is also suitable for use in moving machine parts and the cable chain. It is available as a cable connector, coupling connector or control cabinet feed-through, as well as with insulation displacement or crimp termination. The solid data connectors are now also available with a vibration-proof crimp termination for maximum contact safety.

정보

Cat.6_A acc. to ISO/IEC 11801



Lapp의 보완 자동화 요소



기계 및 플랜트 엔지니어링



조립 시간



간섭 신호

제품 특성

Stability thanks to die-cast zinc metal housing.

Easy cable connection thanks to crimping or insulation displacement technology.

The connector's integrated vibration protection makes it resistant to shocks and vibrations.

UL certification according to technical data enables use of the product in the North American region.

When connected, protection class IP 67 can be achieved.

인증

For use with fine and ultra-fine wire conductors of classes 5 and 6.

Can be used universally on machine interfaces for many applications in data and signal transmission.

For highly flexible, continuously flexing use in moving machine parts and in the cable chain.

Also suitable for EtherCAT, EtherNET/IP and 4-pair PROFINET applications.

기술 데이터

최근 업데이트 (17.02.2024)

©2024 Lapp Group - all rights reserved.

제품 관리 <http://lappkorea.lappgroup.com>

해당하는 data sheet 에서 최근 자료를 찾을 수 있습니다.

PN 0456 / 02_03.16

EPIC® DATA M12X

분류 ETIM 5:	ETIM 5.0 Class-ID: EC001121 ETIM 5.0 클래스 설명 : 모듈 식 커넥터
분류 ETIM 6:	ETIM 6.0 Class-ID: EC001121 ETIM 6.0 Class 설명: 모듈식 커넥터
보호 평가:	IP 67
주변 온도 (작업):	-40 ° C ~ + 85 ° C

비고

사진은 각각의 제품 상세 이미지를 대변하지는 않습니다.
가격은 VAT 및 할증료가 없는 가격. 비즈니스 고객에게만 판매

EPIC® DATA M12X

품번	제품 명칭	최소 외경 (mm)	최대 외경 (mm)	최대. 코어 직경, 절연 포함	AWG solid	AWG 7-wire
M12 X-coded plug, straight						
21700602	ED-IE-AX-M12X-6A-67-FC	6.3	9.7	1.6	26-22	26-22
M12 X-coded socket, straight						
21700621	ED-IE-AX-M12XF-6 _A -67-FC	6.3	9.7	1.6	26-22	26-22
M12 X-coded socket, straight for wall mounting						
21700622	_A -67-FC	6.3	9.7	1.6	26-22	26-22
44429476	-	-	-	4	-	-

EPIC® DATA M12X

