

ETHERLINE® LAN Cat. 6A Patchcords

Screened (S/FTP) RJ45-patchcords - UL-approved

Halogen-free, Cat.6a patchcord for Gigabit Ethernet, with UL approval. Available in different colours and lengths



Lapp



()

IEC 60332-1-2

IEC 60603-7-51 RJ45

UL approvals see data sheet

, 4x2x AWG26/7

S/FTP:

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® LAN Cat. 6A Patchcords

LSZH : 6.2 mm

ETIM 5:

ETIM 5.0 Class-ID: EC002599

ETIM 5.0 class : ()

가:

IP20

:

Installation: 0°C bis +50°C
: -20°C +60°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® LAN Cat. 6A Patchcords

Article number		mm	(m)	
24441316	ETHERLINE LAN Cat.6A 0,25 BK	6.2	0.25	
24441331	ETHERLINE LAN Cat.6A 0,25 BU	6.2	0.25	
24441346	ETHERLINE LAN Cat.6A 0,25 GN	6.2	0.25	
24441361	ETHERLINE LAN Cat.6A 0,25 GY	6.2	0.25	
24441376	ETHERLINE LAN Cat.6A 0,25 OR	6.2	0.25	
24441391	ETHERLINE LAN Cat.6A 0,25 RD	6.2	0.25	
24441406	ETHERLINE LAN Cat.6A 0,25 WH	6.2	0.25	
24441421	ETHERLINE LAN Cat.6A 0,25 YE	6.2	0.25	
24441317	ETHERLINE LAN Cat.6A 0,5 BK	6.2	0.5	
24441332	ETHERLINE LAN Cat.6A 0,5 BU	6.2	0.5	
24441347	ETHERLINE LAN Cat.6A 0,5 GN	6.2	0.5	
24441362	ETHERLINE LAN Cat.6A 0,5 GY	6.2	0.5	
24441377	ETHERLINE LAN Cat.6A 0,5 OR	6.2	0.5	
24441392	ETHERLINE LAN Cat.6A 0,5 RD	6.2	0.5	
24441407	ETHERLINE LAN Cat.6A 0,5 WH	6.2	0.5	
24441422	ETHERLINE LAN Cat.6A 0,5 YE	6.2	0.5	
24441318	ETHERLINE LAN Cat.6A 1,0 BK	6.2	1	
24441333	ETHERLINE LAN Cat.6A 1,0 BU	6.2	1	
24441348	ETHERLINE LAN Cat.6A 1,0 GN	6.2	1	
24441363	ETHERLINE LAN Cat.6A 1,0 GY	6.2	1	
24441378	ETHERLINE LAN Cat.6A 1,0 OR	6.2	1	
24441393	ETHERLINE LAN Cat.6A 1,0 RD	6.2	1	
24441408	ETHERLINE LAN Cat.6A 1,0 WH	6.2	1	
24441423	ETHERLINE LAN Cat.6A 1,0 YE	6.2	1	
24441319	ETHERLINE LAN Cat.6A 1,5 BK	6.2	1.5	
24441334	ETHERLINE LAN Cat.6A 1,5 BU	6.2	1.5	
24441349	ETHERLINE LAN Cat.6A 1,5 GN	6.2	1.5	
24441364	ETHERLINE LAN Cat.6A 1,5 GY	6.2	1.5	
24441379	ETHERLINE LAN Cat.6A 1,5 OR	6.2	1.5	
24441394	ETHERLINE LAN Cat.6A 1,5 RD	6.2	1.5	
24441409	ETHERLINE LAN Cat.6A 1,5 WH	6.2	1.5	
24441424	ETHERLINE LAN Cat.6A 1,5 YE	6.2	1.5	
24441320	ETHERLINE LAN Cat.6A 2,0 BK	6.2	2	
24441335	ETHERLINE LAN Cat.6A 2,0 BU	6.2	2	
24441350	ETHERLINE LAN Cat.6A 2,0 GN	6.2	2	

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® LAN Cat. 6A Patchcords

Article number		mm	(m)	
24441365	ETHERLINE LAN Cat.6A 2,0 GY	6.2	2	
24441380	ETHERLINE LAN Cat.6A 2,0 OR	6.2	2	
24441395	ETHERLINE LAN Cat.6A 2,0 RD	6.2	2	
24441410	ETHERLINE LAN Cat.6A 2,0 WH	6.2	2	
24441425	ETHERLINE LAN Cat.6A 2,0 YE	6.2	2	
24441321	ETHERLINE LAN Cat.6A 3,0 BK	6.2	3	
24441336	ETHERLINE LAN Cat.6A 3,0 BU	6.2	3	
24441351	ETHERLINE LAN Cat.6A 3,0 GN	6.2	3	
24441366	ETHERLINE LAN Cat.6A 3,0 GY	6.2	3	
24441381	ETHERLINE LAN Cat.6A 3,0 OR	6.2	3	
24441396	ETHERLINE LAN Cat.6A 3,0 RD	6.2	3	
24441411	ETHERLINE LAN Cat.6A 3,0 WH	6.2	3	
24441426	ETHERLINE LAN Cat.6A 3,0 YE	6.2	3	
24441322	ETHERLINE LAN Cat.6A 5,0 BK	6.2	5	
24441337	ETHERLINE LAN Cat.6A 5,0 BU	6.2	5	
24441352	ETHERLINE LAN Cat.6A 5,0 GN	6.2	5	
24441367	ETHERLINE LAN Cat.6A 5,0 GY	6.2	5	
24441382	ETHERLINE LAN Cat.6A 5,0 OR	6.2	5	
24441397	ETHERLINE LAN Cat.6A 5,0 RD	6.2	5	
24441412	ETHERLINE LAN Cat.6A 5,0 WH	6.2	5	
24441427	ETHERLINE LAN Cat.6A 5,0 YE	6.2	5	
24441323	ETHERLINE LAN Cat.6A 7,5 BK	6.2	7.5	
24441338	ETHERLINE LAN Cat.6A 7,5 BU	6.2	7.5	
24441353	ETHERLINE LAN Cat.6A 7,5 GN	6.2	7.5	
24441368	ETHERLINE LAN Cat.6A 7,5 GY	6.2	7.5	
24441383	ETHERLINE LAN Cat.6A 7,5 OR	6.2	7.5	
24441398	ETHERLINE LAN Cat.6A 7,5 RD	6.2	7.5	
24441413	ETHERLINE LAN Cat.6A 7,5 WH	6.2	7.5	
24441428	ETHERLINE LAN Cat.6A 7,5 YE	6.2	7.5	
24441324	ETHERLINE LAN Cat.6A 10,0 BK	6.2	10	
24441339	ETHERLINE LAN Cat.6A 10,0 BU	6.2	10	
24441354	ETHERLINE LAN Cat.6A 10,0 GN	6.2	10	
24441369	ETHERLINE LAN Cat.6A 10,0 GY	6.2	10	
24441384	ETHERLINE LAN Cat.6A 10,0 OR	6.2	10	
24441399	ETHERLINE LAN Cat.6A 10,0 RD	6.2	10	

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® LAN Cat. 6A Patchcords

Article number		mm	(m)	
24441414	ETHERLINE LAN Cat.6A 10,0 WH	6.2	10	
24441429	ETHERLINE LAN Cat.6A 10,0 YE	6.2	10	
24441325	ETHERLINE LAN Cat.6A 15,0 BK	6.2	15	
24441340	ETHERLINE LAN Cat.6A 15,0 BU	6.2	15	
24441355	ETHERLINE LAN Cat.6A 15,0 GN	6.2	15	
24441370	ETHERLINE LAN Cat.6A 15,0 GY	6.2	15	
24441385	ETHERLINE LAN Cat.6A 15,0 OR	6.2	15	
24441400	ETHERLINE LAN Cat.6A 15,0 RD	6.2	15	
24441415	ETHERLINE LAN Cat.6A 15,0 WH	6.2	15	
24441430	ETHERLINE LAN Cat.6A 15,0 YE	6.2	15	
24441326	ETHERLINE LAN Cat.6A 20,0 BK	6.2	20	
24441341	ETHERLINE LAN Cat.6A 20,0 BU	6.2	20	
24441356	ETHERLINE LAN Cat.6A 20,0 GN	6.2	20	
24441371	ETHERLINE LAN Cat.6A 20,0 GY	6.2	20	
24441386	ETHERLINE LAN Cat.6A 20,0 OR	6.2	20	
24441401	ETHERLINE LAN Cat.6A 20,0 RD	6.2	20	
24441416	ETHERLINE LAN Cat.6A 20,0 WH	6.2	20	
24441431	ETHERLINE LAN Cat.6A 20,0 YE	6.2	20	
24441327	ETHERLINE LAN Cat.6A 25,0 BK	6.2	25	
24441342	ETHERLINE LAN Cat.6A 25,0 BU	6.2	25	
24441357	ETHERLINE LAN Cat.6A 25,0 GN	6.2	25	
24441372	ETHERLINE LAN Cat.6A 25,0 GY	6.2	25	
24441387	ETHERLINE LAN Cat.6A 25,0 OR	6.2	25	
24441402	ETHERLINE LAN Cat.6A 25,0 RD	6.2	25	
24441417	ETHERLINE LAN Cat.6A 25,0 WH	6.2	25	
24441432	ETHERLINE LAN Cat.6A 25,0 YE	6.2	25	
24441328	ETHERLINE LAN Cat.6A 30,0 BK	6.2	30	
24441343	ETHERLINE LAN Cat.6A 30,0 BU	6.2	30	
24441358	ETHERLINE LAN Cat.6A 30,0 GN	6.2	30	
24441373	ETHERLINE LAN Cat.6A 30,0 GY	6.2	30	
24441388	ETHERLINE LAN Cat.6A 30,0 OR	6.2	30	
24441403	ETHERLINE LAN Cat.6A 30,0 RD	6.2	30	
24441418	ETHERLINE LAN Cat.6A 30,0 WH	6.2	30	
24441433	ETHERLINE LAN Cat.6A 30,0 YE	6.2	30	
24441329	ETHERLINE LAN Cat.6A 40,0 BK	6.2	40	

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® LAN Cat. 6A Patchcords

Article number		mm	(m)	
24441344	ETHERLINE LAN Cat.6A 40,0 BU	6.2	40	
24441359	ETHERLINE LAN Cat.6A 40,0 GN	6.2	40	
24441374	ETHERLINE LAN Cat.6A 40,0 GY	6.2	40	
24441389	ETHERLINE LAN Cat.6A 40,0 OR	6.2	40	
24441404	ETHERLINE LAN Cat.6A 40,0 RD	6.2	40	
24441419	ETHERLINE LAN Cat.6A 40,0 WH	6.2	40	
24441434	ETHERLINE LAN Cat.6A 40,0 YE	6.2	40	
24441330	ETHERLINE LAN Cat.6A 50,0 BK	6.2	50	
24441345	ETHERLINE LAN Cat.6A 50,0 BU	6.2	50	
24441360	ETHERLINE LAN Cat.6A 50,0 GN	6.2	50	
24441375	ETHERLINE LAN Cat.6A 50,0 GY	6.2	50	
24441390	ETHERLINE LAN Cat.6A 50,0 OR	6.2	50	
24441405	ETHERLINE LAN Cat.6A 50,0 RD	6.2	50	
24441420	ETHERLINE LAN Cat.6A 50,0 WH	6.2	50	
24441435	ETHERLINE LAN Cat.6A 50,0 YE	6.2	50	

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16