

# ETHERLINE® PN Cat.5 M12

PROFINET

M12


PVC, UL  
Cat.5 2

Profinet A, M12/M12, D

2170893

가

[www.lappgroup.com/assemblyfinderor](http://www.lappgroup.com/assemblyfinderor)



Lapp



가

EtherCAT EtherNet/IP

(03.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# ETHERLINE® PN Cat.5 M12

Cat.5e class D  
2 : , 10/100Mbit/s

UL : UL/CSA (CMG)  
: E249137

, 2x2x AWG22/1

PVC :  
: (RAL 6018 )  
M12 D 가  
4 M12

ETIM 5: ETIM 5.0 Class-ID: EC002599  
ETIM 5.0 class : ( )

ETIM 6: ETIM 6.0 Class-ID: EC002599  
ETIM 6.0 Class :

:  
: 15 x  
: 10 x

가: IP69

:  
: -20°C to +60°C  
: -40°C +80°C

, 가 가 . ( . ) 가 .  
가 VAT 가 가 .

(03.07.2024)



ETHERLINE® PN Cat.5 M12

Article number		Length (m)	kg/1.000 pieces
M12	M12		
2171001	IE-PNA-5-M12D-S-1-Y-2-22-1-M12D-S	1	30.4
2171002	IE-PNA-5-M12D-S-2-Y-2-22-1-M12D-S	2	60.8
2171003	IE-PNA-5-M12D-S-3-Y-2-22-1-M12D-S	3	91.2
2171004	IE-PNA-5-M12D-S-5-Y-2-22-1-M12D-S	5	152
2171005	IE-PNA-5-M12D-S-10-Y-2-22-1-M12D-S	10	304
2171006	IE-PNA-5-M12D-S-20-Y-2-22-1-M12D-S	20	608
M12	M12		
2171013	IE-PNA-5-M12D-A-1-Y-2-22-1-M12D-S	1	30.4
2171014	IE-PNA-5-M12D-A-2-Y-2-22-1-M12D-S	2	60.8
2171015	IE-PNA-5-M12D-A-3-Y-2-22-1-M12D-S	3	91.2
2171016	IE-PNA-5-M12D-A-5-Y-2-22-1-M12D-S	5	152
2171017	IE-PNA-5-M12D-A-10-Y-2-22-1-M12D-S	10	304
2171018	IE-PNA-5-M12D-A-20-Y-2-22-1-M12D-S	20	608
M12			
2171007	IE-PNA-5-M12D-S-1-Y-2-22-1-OE	1	30.4
2171008	IE-PNA-5-M12D-S-2-Y-2-22-1-OE	2	60.8
2171009	IE-PNA-5-M12D-S-3-Y-2-22-1-OE	3	91.2
2171010	IE-PNA-5-M12D-S-5-Y-2-22-1-OE	5	152
2171011	IE-PNA-5-M12D-S-10-Y-2-22-1-OE	10	304
2171012	IE-PNA-5-M12D-S-20-Y-2-22-1-OE	20	608
M12			
2171019	IE-PNA-5-M12D-A-1-Y-2-22-1-OE	1	30.4
2171020	IE-PNA-5-M12D-A-2-Y-2-22-1-OE	2	60.8
2171021	IE-PNA-5-M12D-A-3-Y-2-22-1-OE	3	91.2
2171022	IE-PNA-5-M12D-A-5-Y-2-22-1-OE	5	152
2171023	IE-PNA-5-M12D-A-10-Y-2-22-1-OE	10	304
2171024	IE-PNA-5-M12D-A-20-Y-2-22-1-OE	20	608

(03.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ETHERLINE® PN Cat.5 M12



(03.07.2024)

©2024 Lapp Group - all rights reserved.  
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16