

ETHERLINE® PN Cat.5 RJ45

PROFINET

RJ45

, Profinet Type A, Cat.5, RJ45, PVC

2170893

가

www.lappgroup.com/assemblyfinderor



Lapp



2

가

EtherCAT EtherNet/IP

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ETHERLINE® PN Cat.5 RJ45

Cat.5e class D
2 : , 10/100Mbit/s

: UL/CSA (CMG)

, 2x2x AWG22/1

:
PVC
: (RAL 6018)
RJ45 가

ETIM 5:

ETIM 5.0 Class-ID: EC002599
ETIM 5.0 class : ()

ETIM 6:

ETIM 6.0 Class-ID: EC002599
ETIM 6.0 Class :

:

: 15 x
: 10 x

가:

IP20

:

: -20°C to +60°C
: -40°C +80°C

, 가 가 . (.) 가 .
가 VAT 가 가 .



ETHERLINE® PN Cat.5 RJ45

Article number		(m)	kg/1.000 pieces
RJ45	RJ45		
2171178	IE-PNA-5-RJ45-0,5-Y-2-22-1-RJ45	0.5	15.2
2171179	IE-PNA-5-RJ45-1-Y-2-22-1-RJ45	1	30.4
2171180	IE-PNA-5-RJ45-2-Y-2-22-1-RJ45	2	60.8
2171181	IE-PNA-5-RJ45-3-Y-2-22-1-RJ45	3	91.2
2171182	IE-PNA-5-RJ45-5-Y-2-22-1-RJ45	5	152
2171183	IE-PNA-5-RJ45-10-Y-2-22-1-RJ45	10	304
2171184	IE-PNA-5-RJ45-20-Y-2-22-1-RJ45	20	608
	RJ45		
2171185	IE-PNA-5-RJ45-0,5-Y-2-22-1-OE	0.5	15.2
2171186	IE-PNA-5-RJ45-1-Y-2-22-1-OE	1	30.4
2171187	IE-PNA-5-RJ45-2-Y-2-22-1-OE	2	60.8
2171188	IE-PNA-5-RJ45-3-Y-2-22-1-OE	3	91.2
2171189	IE-PNA-5-RJ45-5-Y-2-22-1-OE	5	152
2171190	IE-PNA-5-RJ45-10-Y-2-22-1-OE	10	304
2171191	IE-PNA-5-RJ45-20-Y-2-22-1-OE	20	608