

ETHERLINE® PN Flex Cat.5 M12

PROFINET

M12

, Profinet Type B, Cat.5,

M12, D

PVC,

2170886

가

www.lappgroup.com/assemblyfinderor



Lapp



2

가

EtherCAT EtherNet/IP

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® PN Flex Cat.5 M12

Cat.5e class D
2 : , 10/100Mbit/s

UL : UL/CSA (CMG)
: E249137

Braided conductor, 2x2x AWG22/7

PVC :
: (RAL 6018)
M12 D 가
4 M12

ETIM 5: ETIM 5.0 Class-ID: EC002599
ETIM 5.0 class : ()

ETIM 6: ETIM 6.0 Class-ID: EC002599
ETIM 6.0 Class :

: : 15 x
: 10 x

가: IP69

: : -20°C +60°C
: -40°C +80°C

, 가 가 . (.) 가 .
가 VAT 가 가 .

(22.07.2024)



ETHERLINE® PN Flex Cat.5 M12

Article number		Length (m)	kg/1.000 pieces
M12	M12		
2171025	IE-PNB-5-M12D-S-1-Y-2-22-7-M12D-S	1	31.3
2171026	IE-PNB-5-M12D-S-2-Y-2-22-7-M12D-S	2	62.6
2171027	IE-PNB-5-M12D-S-3-Y-2-22-7-M12D-S	3	93.9
2171028	IE-PNB-5-M12D-S-5-Y-2-22-7-M12D-S	5	156.5
2171029	IE-PNB-5-M12D-S-10-Y-2-22-7-M12D-S	10	313
2171030	IE-PNB-5-M12D-S-20-Y-2-22-7-M12D-S	20	626
M12	M12		
2171037	IE-PNB-5-M12D-A-1-Y-2-22-7-M12D-S	1	31.3
2171038	IE-PNB-5-M12D-A-2-Y-2-22-7-M12D-S	2	62.6
2171039	IE-PNB-5-M12D-A-3-Y-2-22-7-M12D-S	3	93.9
2171040	IE-PNB-5-M12D-A-5-Y-2-22-7-M12D-S	5	156.5
2171041	IE-PNB-5-M12D-A-10-Y-2-22-7-M12D-S	10	313
2171042	IE-PNB-5-M12D-A-20-Y-2-22-7-M12D-S	20	626
M12			
2171031	IE-PNB-5-M12D-S-1-Y-2-22-7-OE	1	31.3
2171032	IE-PNB-5-M12D-S-2-Y-2-22-7-OE	2	62.6
2171033	IE-PNB-5-M12D-S-3-Y-2-22-7-OE	3	93.9
2171034	IE-PNB-5-M12D-S-5-Y-2-22-7-OE	5	156.5
2171035	IE-PNB-5-M12D-S-10-Y-2-22-7-OE	10	313
2171036	IE-PNB-5-M12D-S-20-Y-2-22-7-OE	20	626
M12			
2171043	IE-PNB-5-M12D-A-1-Y-2-22-7-OE	1	31.3
2171044	IE-PNB-5-M12D-A-2-Y-2-22-7-OE	2	62.6
2171045	IE-PNB-5-M12D-A-3-Y-2-22-7-OE	3	93.9
2171046	IE-PNB-5-M12D-A-5-Y-2-22-7-OE	5	156.5
2171047	IE-PNB-5-M12D-A-10-Y-2-22-7-OE	10	313
2171048	IE-PNB-5-M12D-A-20-Y-2-22-7-OE	20	626

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ETHERLINE® PN Flex Cat.5 M12



(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16